



EW-7811Un

## 150Mbps Wireless IEEE802.11b/g/n nano USB Adapter



EW-7811Un is a nano USB wireless adapter that supports maximum range and speed. Despite the size, this tiny USB adapter supports higher data rate of up to 150Mbps when connecting with wireless 802.11n device which is 3 times faster than your normally 11g connection. You can just plug it into computer's USB port and enjoy incredible high-speed wireless network access. This is for sure the trendiest piece of upgrade you can make to your wireless network.

### Complies with wireless 802.11n standards with data rate up to 150Mbps

EW-7811Un complies with wireless IEEE802.11b/g/n standards. As being built with the latest wireless technology, the EW-7811Un can increase your wireless coverage up to 3 times as much and greatly help reduce "dead spots" compared to your old 11g adapter. The transmission data rate can go up to 150Mbps when connected to a 802.11n device, with signal travel further and connection a lot more stable compared to your previous 802.11g network .

### Supports Green WLAN

EW-7811Un has adapted a clever protocol in smart transmission power control. The adapter smartly adjust transmission output by distance and CPU offload to help reduce power consumption when wireless is idle. With the green WLAN technology, the power consumption can be reduced up to 20% ~ 50%. The adapter does not just provide you with the best wireless technology in the world, it also care for the environment by using less energy and your pocket by saving up on your electric bills.

### Supports WPS (Wi-Fi Protected Setup)

Wi-Fi Protected Setup (WPS) is a standard for easy and secure establishment of a wireless network. This wireless USB adapter supports software WPS-compatible configuration. By pressing 2 buttons, your wireless network is immediately secured providing your wireless router will also support this great easy function.

### Supports multi-language EZmax setup wizard

The included 16 languages EZmax setup wizard and friendly UI will walk you through configuring EW-7811Un to your wireless network.

### Portable and compact design

EW-7811Un is currently the smallest wireless adapter. The compact design of EW-7811Un is convenient to carry for all mobile users. It also means you will not be able to accidentally snap your USB adapter anymore as it is hidden very well once it is plugged into the USB port.

\* The EZMax Setup CD Wizard only supports Edimax wireless Series.

**FEATURES AND TECHNICAL SPECIFICATIONS**

- ✦ Complies with wireless 802.11b/g/n standards with data rate up to 150Mbps
- ✦ Green Power Saving : supports smart transmit power control and auto-idle state adjustment
- ✦ Increases wireless coverage 3 times further☺
- ✦ Includes multi-language EZmax setup wizard.
- ✦ Supports 64/128-bit WEP, WPA , WPA2 encryption and WPS-compatible.
- ✦ Supports QoS-WMM, WMM-Power Save mode

HARDWARE INTERFACE	STANDARD	FREQUENCY BAND
<ul style="list-style-type: none"> <li>✦ 1 USB 1.0/2.0 Type A</li> <li>✦ Internal Antenna</li> </ul>	<ul style="list-style-type: none"> <li>✦ IEEE802.11b, 802.11g, 802.11n</li> </ul>	<ul style="list-style-type: none"> <li>✦ 2.4000~2.4835GHz (Industrial Scientific Medical Band)</li> </ul>

DATA RATE	INSTALLATION	LED & DIMENSION
<ul style="list-style-type: none"> <li>✦ 11b: 1/2/5.5/11Mbps</li> <li>✦ 11g: 6/9/12/24/36/48/54Mbps</li> <li>✦ 11n (20MHz): MCS0-7 (up to 72Mbps)</li> <li>✦ 11n (40MHz): MCS0-7 (up to 150Mbps)</li> </ul>	<ul style="list-style-type: none"> <li>✦ Multi-language EZmax Setup Wizard</li> </ul>	<ul style="list-style-type: none"> <li>✦ Link/Activity</li> <li>✦ 7.1(H) x 14.9 (W) x 18.5 (D) mm</li> </ul>

SECURITY	OUTPUT POWER	HUMIDITY & TEMPERATURE
<ul style="list-style-type: none"> <li>✦ WEP 64/128, WPA, WPA2, and IEEE802.1x</li> <li>✦ Software WPS configuration</li> </ul>	<ul style="list-style-type: none"> <li>✦ 11b:17 ± 1.5dbm</li> <li>✦ 11g:b:15 ± 1.5dbm</li> <li>✦ 11n:14 ± 1.5dbm</li> </ul>	<ul style="list-style-type: none"> <li>✦ Operating : 10~90% (Non Condensing)</li> <li>✦ Storage : Max. 95% (Non Condensing)</li> <li>✦ Operating : 32~104°F (0~40°C)</li> <li>✦ Storage : -4~140°F (-20~60°C)</li> </ul>

SYSTEM REQUIREMENTS	RECEIVE SENSITIVITY	CERTIFICATIONS
<ul style="list-style-type: none"> <li>✦ Windows XP/Vista/7</li> <li>✦ Linux &amp; Mac OS</li> </ul>	<ul style="list-style-type: none"> <li>✦ 11n(20MHz)@MCS7: -68dBm±2dBm</li> <li>✦ 11n(40MHz)@MCS7: -64dBm±2dBm</li> <li>✦ 11g@54Mbps: -71dBm±2dBm</li> <li>✦ 11b@11Mbps: -81dBm±2dBm</li> </ul>	<ul style="list-style-type: none"> <li>✦ CE, FCC , WiFi</li> </ul>

**NETWORK SETUP DIAGRAM AND RELATED PRODUCTS**

An example of how the EW-7811Un can be setup:

- Connects the EW-7811Un wireless adapter to your computer.
- Setups the wireless connection by running the multi-language EZmax wizard.
- Connects to 802.11b/g/n wireless access point or broadband router.

