

For more Information  
please call

1-800-Belden1



## General Description:

RG-8/U type, 13 AWG stranded (7x21) .085" bare copper conductor, polyethylene insulation, bare copper braid shield (95% coverage), PVC jacket.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	13	7x21	BC - Bare Copper	.085

Total Number of Conductors: 1

### Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PE - Polyethylene	.285

### Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	95.000

### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

### Overall Cable

Overall Nominal Diameter: 0.403 in.

## Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 106 lbs/1000 ft.

Max. Recommended Pulling Tension: 190 lbs.

Min. Bend Radius/Minor Axis: 4.250 in.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMH
CEC/C(UL) Specification:	CMH
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Military Specification:	JAN-C-17A
RG Type:	8/U

**Flame Test**

CSA Flame Test: FT1

**Suitability**

Suitability - Indoor: Yes

**Plenum/Non-Plenum**

Plenum (Y/N): No

**Electrical Characteristics (Overall)**

**Nom. Characteristic Impedance:**

Impedance (Ohm)

52

**Nom. Inductance:**

Inductance (µH/ft)

.079

**Nom. Capacitance Conductor to Shield:**

Capacitance (pF/ft)

28.5

**Nominal Velocity of Propagation:**

VP (%)

66

**Nominal Delay:**

Delay (ns/ft)

1.54

**Nom. Conductor DC Resistance:**

DCR @ 20°C (Ohm/1000 ft)

1.9

**Nominal Outer Shield DC Resistance:**

DCR @ 20°C (Ohm/1000 ft)

1.2

**Nom. Attenuation:**

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.2
10	.6
50	1.3
100	1.9
200	2.8
400	4.2
700	5.9
900	6.9
1000	7.4
4000	23.2

**Nom. Power Rating:**

Freq. (MHz)	Rating (W)
50	1200
100	800
400	320
1000	180

**Max. Operating Voltage - Non-UL:**

Voltage

3700 V RMS

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8237 010100	100 FT	13.200 LB	BLACK	C	RG-8/U JAN-C-17A COAX
8237 0101000	1,000 FT	111.000 LB	BLACK	C	RG-8/U JAN-C-17A COAX
8237 010500	500 FT	56.000 LB	BLACK	C	RG-8/U JAN-C-17A COAX

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 07-30-2013

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.  
Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.  
All sales of Belden products are subject to Belden's standard terms and conditions of sale.  
Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.