



Revision Number: 005.0

Issue date: 02/17/2017

**1. PRODUCT AND COMPANY IDENTIFICATION**

**Product name:** LOCTITE 366 HMP 5C 0.56MM R  
known as HMP 366 5C 0.56MM 0.25KG AM (0)

**Product type:** Solder Wire

**Restriction of Use:** None identified

**Company address:**  
Henkel Corporation  
One Henkel Way  
Rocky Hill, Connecticut 06067

**IDH number:** 397952

**Item number:** MM01006

**Region:** United States

**Contact information:**  
Telephone: (860) 571-5100  
MEDICAL EMERGENCY Phone: Poison Control Center  
1-877-671-4608 (toll free) or 1-303-592-1711  
TRANSPORT EMERGENCY Phone: CHEMTREC  
1-800-424-9300 (toll free) or 1-703-527-3887  
Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**DANGER:** MAY CAUSE DROWSINESS OR DIZZINESS.  
SUSPECTED OF CAUSING CANCER.  
MAY DAMAGE FERTILITY OR THE UNBORN CHILD.  
CAUSES DAMAGE TO ORGANS THROUGH PROLONGED OR REPEATED EXPOSURE.

HAZARD CLASS	HAZARD CATEGORY
CARCINOGENICITY	2
REPRODUCTIVE TOXICITY	1B
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3
SPECIFIC TARGET ORGAN TOXICITY - REPEATED EXPOSURE	1

**PICTOGRAM(S)**



**Precautionary Statements**

**Prevention:** Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not breathe dust or fumes. Wash affected area thoroughly after handling. Do not eat, drink or smoke when using this product. Use only outdoors or in a well-ventilated area. Wear protective gloves, clothing, eye and face protection.

**Response:** IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell. IF exposed or concerned: Get medical attention.

**Storage:** Store in a well-ventilated place. Keep container tightly closed. Store locked up.

**Disposal:** Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Lead	7439-92-1	90 - 100
Tin	7440-31-5	1 - 5
Silver	7440-22-4	1 - 5

\* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
<b>Skin contact:</b>	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. If symptoms develop and persist, get medical attention. Wash clothing before reuse.
<b>Eye contact:</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	Do not induce vomiting. Never give anything by mouth to an unconscious person. Get medical attention.
<b>Symptoms:</b>	See Section 11.

### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. Do not use water on fires where molten metal is present.
<b>Unusual fire or explosion hazards:</b>	In case of fire, keep containers cool with water spray.
<b>Hazardous combustion products:</b>	Oxides of carbon. Oxides of Metals in Section 3. Formaldehyde. High temperatures may produce heavy metal dust, fumes or vapours. The flux medium will give rise to irritating fumes.

### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Ensure adequate ventilation. Wear suitable protective clothing, gloves and eye/face protection. Scrape up spilled material and place in a closed container for disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

## 7. HANDLING AND STORAGE

- Handling:** Use only in well-ventilated areas. Wear suitable protective clothing, gloves and eye/face protection. Avoid contact with eyes, skin and clothing. When using, do not eat, drink or smoke. Wash thoroughly after handling.
- Storage:** Keep the container tightly closed and in a cool, well-ventilated place. Store in original container until ready to use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Lead	0.05 mg/m <sup>3</sup> TWA (as Pb)	0.05 mg/m <sup>3</sup> TWA 0.03 mg/m <sup>3</sup> OSHA_ACT	None	None
Tin	2 mg/m <sup>3</sup> TWA	2 mg/m <sup>3</sup> PEL (as Sn)	None	None
Silver	0.1 mg/m <sup>3</sup> TWA Dust and fume.	0.01 mg/m <sup>3</sup> PEL (as Ag)	None	None

- Engineering controls:** Use adequate ventilation to remove molten vapors or fumes.
- Respiratory protection:** Use an organic vapor respirator for concentrations exceeding the Occupational Exposure Limit.
- Eye/face protection:** Safety goggles or safety glasses with side shields.
- Skin protection:** Disposable rubber or plastic gloves.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

- Physical state:** Solid, Paste
- Color:** Gray
- Odor:** Mild
- Odor threshold:** Not available.
- pH:** Not available.
- Vapor pressure:** Not available.
- Boiling point/range:** Not available.
- Melting point/ range:** Not available.
- Specific gravity:** 11.1
- Vapor density:** Not available.
- Flash point:** > 100 °C (> 212°F)
- Flammable/Explosive limits - lower:** Not available.
- Flammable/Explosive limits - upper:** Not available.
- Autoignition temperature:** Not available.
- Flammability:** Not applicable
- Evaporation rate:** Not available.
- Solubility in water:** Insoluble
- Partition coefficient (n-octanol/water):** Not available.
- VOC content:** < 5 %
- Viscosity:** Not available.
- Decomposition temperature:** Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	Will not occur.
<b>Hazardous decomposition products:</b>	Oxides of carbon. Oxides of Metals in Section 3. Formaldehyde. Thermal decomposition can lead to release of irritating gases and vapors.
<b>Incompatible materials:</b>	Strong oxidizing agents. Strong acids and strong bases.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.

## 11. TOXICOLOGICAL INFORMATION

**Relevant routes of exposure:** Skin, Inhalation, Eyes, Ingestion

**Potential Health Effects/Symptoms**

<b>Inhalation:</b>	Inhalation of processing fumes may be harmful. Vapor overexposure may cause drowsiness. Dizziness. Fumes and/or dust produced by this product may be hazardous in case of ingestion or inhalation. Rosin thermal decomposition product (as formaldehyde) is classified by NIOSH as a potential occupational carcinogen. Excessive exposure to tin fumes or dust may cause Stannosis, a chronic respiratory disease resulting in reduced lung capacity and benign tumors. Lead is a cumulative poison and continuous exposure to small amounts over time can raise the body's content to toxic levels. Excessive inhalation of fumes from many metals can produce an acute reaction known as "metal fume fever". Symptoms consist of chills and fever (very similar to and easily confused with flu symptoms) which come on a few hours after large exposures.
<b>Skin contact:</b>	May be harmful if absorbed through skin. Argyria (a non-toxic, cosmetic blue-gray discoloration of the skin and mucous membranes that is irreversible). May cause skin irritation.
<b>Eye contact:</b>	Fumes released during thermal processing may cause eye irritation. Contact with eyes will cause irritation.
<b>Ingestion:</b>	May be toxic if swallowed. Lead is a cumulative poison and continuous exposure to small amounts over time can raise the body's content to toxic levels. Symptoms of lead poisoning include abdominal pain, nausea, vomiting, and headache.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Lead	None	Behavioral, Blood, Developmental, Eyes, Gastrointestinal, Kidney, Liver, Muscle, Nervous System, Reproductive, Skin, Some evidence of carcinogenicity, Thyroid
Tin	None	Gastrointestinal, Irritant, Kidney, Liver, Lung, Nervous System
Silver	Oral LD50 (Rat) = > 5,000 mg/kg Dermal LD50 (Rat) = > 2,000 mg/kg	Allergen, Eyes, Irritant, Respiratory, Skin

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Lead	Reasonably Anticipated to be a Human Carcinogen.	Group 2B	No
Tin	No	No	No
Silver	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

### 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.  
**Hazardous waste number:** D011. Silver. D008: Lead

### 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

#### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

#### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

#### Water Transportation (IMO/IMDG)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### 15. REGULATORY INFORMATION

#### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.  
**TSCA 12 (b) Export Notification:** None above reporting de minimis  
**CERCLA/SARA Section 302 EHS:** None above reporting de minimis.  
**CERCLA/SARA Section 311/312:** Immediate Health, Delayed Health  
**CERCLA/SARA Section 313:** This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Lead (CAS# 7439-92-1). Silver (CAS# 7440-22-4).  
**CERCLA Reportable quantity:** Lead (CAS# 7439-92-1) 10 lbs. (4.54 kg)  
**California Proposition 65:** This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

#### Canada Regulatory Information

**CEPA DSL/NDL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

### 16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

**Prepared by:** Alicia Griffin, Regulatory Affairs Specialist  
**Issue date:** 02/17/2017

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.