



# Point of Use Ionizing Blower

## MODEL 6432E





The Point of Use Ionizing Blower Model 6432e control static discharge in assembly, inspection, packaging areas, and in-tool wherever static build-up can cause contamination, ESD, material-handling problems or microprocessor lock-up.

IsoStat technology makes ION Systems blowers the most reliable ionizers available. IsoStat characteristics include small size and operation without grounding wires or cables while still maintaining ionizer balance. The Blower's internal emitter points are electrostatically shielded to eliminate field-induced charging. Steady-state DC ion emission to provide fast discharge with low airflow for greater operator comfort, the Model 6432e Blower offers the best of IsoStat technology.

### Features and Benefits

- IsoStat® technology
- Steady-state DC ion emission
- 24 VDC or 24 VAC input power
- Facility Monitoring System (FMS) interface
- Operational failure alarm
- Small footprint design with in-tool stand or benchtop stand
- Intrinsically balanced; no calibration needed
- Minimum ion recombination provides maximum static control
- Convenient power options, wall-provided AC or tool-provided DC
- Faster response to ionization failure with notification through tool or facility monitoring system
- Provides visual notification of any operational failures
- Occupies little work or tool space; cleanroom-compatible (minimizes disruption of laminar flow)

# Specifications

<b>Input Voltage</b>	24 VDC ( $\pm 10\%$ ), 6W max or 24 VAC ( $\pm 10\%$ ), 50-60 Hz, 6W max
<b>Indicators</b>	Green power LED; red alarm LED
<b>Ion Emission</b>	Steady-state DC
<b>Emitter Points</b>	Tungsten wire; internally shielded
<b>Airflow</b>	49 CFM, typical
<b>Discharge</b>	$\pm 1000$ -100V <4 sec @ 1 ft <sup>1</sup> (using 24 VAC)
<b>Balance</b>	$\pm 20$ V @ 1 ft away
<b>Ozone</b>	<0.005 ppm, typical (24-hour accumulation)
<b>Mounting</b>	Small in-tool bracket/stand (1.8 x 5.1 in./45 x 129 mm); large benchtop stand (4.1 x 5.1 in./108 x 129 mm); both with 1/4" mounting hole and 10-32 truss head screws
<b>Dimensions</b>	5.3H x 5.0W x 2.5D (133 x 127 x 63 mm); small bracket base is 1.8 in. (45 mm); large stand base is 4.1 in. (108 mm)
<b>Weight</b>	21 oz (595g) with large stand
<b>Warranty</b>	2-year warranty
<b>Certifications</b>	
<b>Transformer 14-1320</b>	
<b>Input Voltage</b>	120 VAC $\pm 10\%$ , 50-60 Hz
<b>Output</b>	24 VAC, 60 Hz @ 450 mA, $\pm 5\%$
<b>Dimensions</b>	2.4H x 2.2W x 1.6D in. (61 x 56 x 41 mm)
<b>Certifications</b>	
<b>Transformer 14-1330</b>	
<b>Input Voltage</b>	230 VAC $\pm 10\%$ , 50 Hz
<b>Output</b>	24 VAC @ 750 mA, $\pm 5\%$
<b>Dimensions</b>	2.8H x 2.5W x 1.9D in. (71H x 64W x 48D mm)
<b>Certifications</b>	
<b>AC Adapter 14-1322</b>	
<b>Input Voltage</b>	120-240 VAC $\pm 10\%$ , 50/60 Hz
<b>Output</b>	24 VDC @ 400 mA
<b>Dimensions</b>	1.4H x 2.1W x 3.4L in. (36H x 53W x 86L mm)
<b>Certifications</b>	

1. Tested in accordance with ANSI/ESD STM3.1-2006.

## Ordering Information

<b>91-6432e</b>	Blower with alarm indicator light and FMS
<b>32-6433</b>	Benchtop stand
<b>32-6434</b>	In-tool stand
<b>14-1320</b>	24 VAC 120V 60 Hz transformer
<b>14-1330</b>	24 VAC 230V 50 Hz transformer
<b>14-1322</b>	24 VDC 120/230V 50/60 Hz AC-DC adapter

## Enhanced Features

The Model 6432e offers both an alarm LED on the front of the blower that indicates a high voltage circuitry failure, and a five-pin facility monitoring system (FMS) interface. The FMS interface provides a 4-20 mA current loop and relay output connection. Together with the 24 VDC input connection, the FMS output is situated on a convenient terminal block, designed for easy integration with your process equipment.



## Power Options

For increased flexibility, the Model 6432e Blower can be directly powered by process equipment or 24 VDC/VAC power to fit the needs of your environment. For 100-120 VAC input power, use transformer #14-1320; for 240-260 VAC, use #14-1330; for applications where DC input power is preferable, use AC/DC adapter #14-1322.



The Model 6432e is offered with a smaller in-tool stand (shown here) or a larger benchtop stand.



## ION Systems

1750 North Loop Road  
Alameda, CA 94502

Tel: 800.367.2452 (in USA)  
Tel: 510.217.0600  
info@ion.com  
www.ion.com