

FTSH





LEAD

(1.27 mm) .050"

T MICRO HEADER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FTSH

Insulator Material:

Black Liquid Crystal Polymer Terminal Material: Phosphor Bronze

Plating: Sn or Au over 50 µ" (1.27 µm) Ni Current Rating (FTSH/CLP):

3.4 A per pin
(2 pins powered)
Operating Temp Range:
-55 °C to +125 °C
ROHS Compliant:

PROCESSING

Lead-Free Solderable:

SMT Lead Coplanarity:

-MT & -DV Tail Option: (0.10 mm) .004" max (02-25) -MT & -DH Tail Option: (0.15 mm) .006" max (26-50)* *(.004" stencil solution may be available; contact IPG@samtec.com)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




ALSO AVAILABLE (MOQ Required)


- · Molded Pick & Place pads
- Latches
- · Other platings Contact Samtec.

Some sizes, styles and options are non-standard, non-returnable.


See SFM/TFM for positive alignment feature.




NO. PINS




FTSH-112-02-L-DH



FTSH SERIES





Due to technical progress, all designs, specifications and components are subject to change without notice.