

Kingbright

Kingbright Electronic Europe GmbH



Low Current SMD LED

- Compact sizes including 0402, 0603, 0805, 1206 and many other options
- Available in various colour selections: blue, green, yellow, orange, red and bi-colour
- Different viewing angles vary from 10° to 140° for design requirements
- Mounting options include top-mount and right angle
- Chip type, PLCC, and subminiature options
- Flexible colour combinations in bi-colour combinations available upon request
- Robust and high reliability with competitive lead time

LOW CURRENT SMD LED

Part Number	Material	λD (nm)	Lens Type	Iv (mcd) @2mA		Viewing Angle 2θ1/2	Dimensions
				Min.	Typ.		
KPHHS-1005LVSECK-J3-PF	AlGaInP	625	Water Clear	15	35	120°	<p>1.0mm x 0.5mm x 0.5mm (0402)</p> <p>LED Chip</p> <p>KPHHS-1005LV</p> <p>LVZGCK LVQBC-D</p> <p>LED Chip</p> <p>Units: mm (inch) Tolerance: ± 0.1 (0.004)</p>
KPHHS-1005LVSECK-J4-PF	AlGaInP	605	Water Clear	20	40	120°	
KPHHS-1005LVSYCK-J3-PF	AlGaInP	590	Water Clear	10	20	120°	
KPHHS-1005LVCGCK	AlGaInP	570	Water Clear	1.2	3.5	120°	
KPHHS-1005LVZGCK	InGaN	525	Water Clear	20	40	140°	
KPHHS-1005LVQBC-D	InGaN	465	Water Clear	6	15	140°	
KPHD-1608LVSURCK	AlGaInP	630	Water Clear	4	15	100°	<p>1.6mm x 0.8mm x 0.65mm (0603)</p> <p>Polarity mark</p> <p>KPHD-1608LV</p> <p>Polarity mark</p> <p>Units: mm (inch) Tolerance: ± 0.15 (0.006)</p>
KPHD-1608LVSYCK	AlGaInP	590	Water Clear	4	20	100°	
KPHD-1608LVCGCK	AlGaInP	570	Water Clear	2	8	100°	
KPHD-1608LVZGCK	InGaN	525	Water Clear	50	180	100°	
KPHD-1608LVVBC-D	InGaN	470	Water Clear	15	45	100°	
KPHD-1608LVQBC-D	InGaN	465	Water Clear	10	25	100°	
KPT-1608LVSECK-J3-PRV	AlGaInP	625	Water Clear	20	40	120°	<p>1.6mm x 0.8mm x 0.75mm (0603)</p> <p>1608xxxPRV</p> <p>KPT-1608LV</p> <p>Polarity mark</p> <p>Units: mm (inch) Tolerance: ± 0.1 (0.004)</p>
KPT-1608LVSECK-J4-PRV	AlGaInP	605	Water Clear	30	50	120°	
KPT-1608LVSYCK-J3-PRV	AlGaInP	590	Water Clear	15	25	120°	
KPT-1608LVZGCK	InGaN	525	Water Clear	50	100	130°	
KPT-1608LVVBC-D	InGaN	470	Water Clear	15	24	130°	
KPTD-1608LVSECK-J3-PF	AlGaInP	625	Water Clear	20	50	60°	
KPTD-1608LVSECK-J4-PF	AlGaInP	605	Water Clear	80	150	60°	
KPTD-1608LVSYCK-J3-PF	AlGaInP	590	Water Clear	30	55	60°	
KPTD-1608LVZGCK	InGaN	525	Water Clear	120	220	60°	
KPTD-1608LVVBC-D	InGaN	470	Water Clear	30	65	40°	
KPTD-1608LVQBC-D	InGaN	465	Water Clear	30	65	40°	

LOW CURRENT SMD LED

Part Number	Material	λD (nm)	Lens Type	Iv (mcd) @2mA		Viewing Angle 2θ1/2	Dimensions
				Min.	Typ.		
KPT-2012LVSECK-J3-PRV	AlGaInP	625	Water Clear	20	40	140°	<p>2.0mm x 1.25mm x 0.75mm (0805)</p> <p>KPT-2012LV</p> <p>2012xxxPRV</p> <p>0.13(0.005) Polarity mark</p> <p>1.25(0.049)</p> <p>2(0.079)</p> <p>1.3(0.051)</p> <p>1.2(0.047)</p> <p>0.75(0.03)</p> <p>0.25(0.01)</p> <p>1.25(0.049)</p> <p>0.4(0.016) 0.4(0.016)</p> <p>1 2</p> <p>1 2</p> <p>Units: mm (inch) Tolerance: ± 0.1 (0.004)</p>
KPT-2012LVSECK-J4-PRV	AlGaInP	605	Water Clear	30	50	140°	
KPT-2012LVSYCK-J3-PRV	AlGaInP	590	Water Clear	15	25	140°	
KPT-2012LVZGCK	InGaN	525	Water Clear	20	50	140°	
KPT-2012LVVBC-D	InGaN	470	Water Clear	15	24	140°	
KPTD-2012LVSURCK	AlGaInP	630	Water Clear	20	50	40°	
KPTD-2012LVSYCK	AlGaInP	590	Water Clear	30	90	40°	
KPTD-2012LVCGCK	AlGaInP	570	Water Clear	20	40	40°	
KPTD-2012LVZGCK	InGaN	525	Water Clear	180	440	40°	
KPTD-2012LVVBC-D	InGaN	470	Water Clear	30	90	30°	
KPTD-2012LVQBC-D	InGaN	465	Water Clear	20	50	30°	
KPA-2107LVSECK-J3-PRV	AlGaInP	625	Water Clear	15	30	140°	<p>2.1mm x 1.0mm x 0.6mm (Right Angle)</p> <p>KPA-2107LV</p> <p>2.1(0.083)</p> <p>0.15(0.006) 0.15(0.006)</p> <p>0.6(0.024)</p> <p>1.7(0.067)</p> <p>R0.6(0.024)</p> <p>0.5(0.02) 1(0.039)</p> <p>0.3(0.012) 0.3(0.012)</p> <p>1 2</p> <p>1 2</p> <p>Units: mm (inch) Tolerance: ± 0.1 (0.004)</p>
KPA-2107LVSECK-J4-PRV	AlGaInP	605	Water Clear	20	40	140°	
KPA-2107LVSYCK-J3-PRV	AlGaInP	590	Water Clear	15	30	140°	
KPA-2107LVZGCK	InGaN	525	Water Clear	20	40	170°	
KPA-2107LVVBC-D	InGaN	470	Water Clear	10	20	170°	
KA-3021LVSESK-J3-TR	AlGaInP	625	Water Clear	20	45	120°	
KA-3021LVSESK-J4-TR	AlGaInP	605	Water Clear	30	60	120°	
KA-3021LVSYSK-J3-TR	AlGaInP	590	Water Clear	20	45	120°	
KA-3021LVZGSK	InGaN	525	Water Clear	80	180	120°	
KA-3021LVVBS-D	InGaN	470	Water Clear	20	50	120°	


LOW CURRENT SMD LED

Part Number	Material	λD (nm)	Lens Type	Iv (mcd) @2mA		Viewing Angle 2θ1/2	Dimensions
				Min.	Typ.		
KPDA-3020LVSECK-J3-PF	AlGaInP	625	Water Clear	250	500	10°	<p>3.0mm x 2.8mm x 2.0mm (Right Angle)</p> <p>KPDA-3020LV LVZGCK LVWBC-D 1 ♂ → 2</p> <p>SECK-J3-PF SECK-J4-PF SYCK-J3-PF 1 ♂ → 2</p> <p>Units: mm (inch) Tolerance: ± 0.2 (0.008)</p>
KPDA-3020LVSECK-J4-PF	AlGaInP	605	Water Clear	550	1000	10°	
KPDA-3020LVSYCK-J3-PF	AlGaInP	590	Water Clear	180	500	10°	
KPDA-3020LVZGCK	InGaIn	525	Water Clear	250	600	10°	
KPDA-3020LVWBC-D	InGaIn	470	Water Clear	80	150	10°	
KPT-3216LVSECK-J3-PRV	AlGaInP	625	Water Clear	20	40	140°	
KPT-3216LVSECK-J4-PRV	AlGaInP	605	Water Clear	30	50	140°	
KPT-3216LVSYCK-J3-PRV	AlGaInP	590	Water Clear	15	25	140°	
KPT-3216LVZGCK	InGaIn	525	Water Clear	20	50	150°	
KPT-3216LVWBC-D	InGaIn	470	Water Clear	15	24	150°	
KPTD-3216LVSURCK	AlGaInP	630	Water Clear	20	50	40°	<p>3.2mm x 1.6mm x 1.8mm (1206 Dome Lens)</p> <p>KPTD-3216LV Polarity mark 1 ♂ → 2</p> <p>Units: mm (inch) Tolerance: ± 0.2 (0.008)</p>
KPTD-3216LVSYCK	AlGaInP	590	Water Clear	18	40	40°	
KPTD-3216LVCGCK	AlGaInP	570	Water Clear	15	25	40°	
KPTD-3216LVZGCK	InGaIn	525	Water Clear	180	290	30°	
KPTD-3216LVWBC-D	InGaIn	470	Water Clear	50	120	30°	
KPTD-3216LVQBC-D	InGaIn	465	Water Clear	40	100	30°	
KA-3528LVSECKT-J3	AlGaInP	625	Water Clear	30	50	120°	<p>3.5mm x 2.8mm x 1.9mm</p> <p>KA-3528LV LVZGCKT LVWBS-D 2 ♂ → 1</p> <p>SECKT-J3 SECKT-J4 SYCKT-J3 2 ♂ → 1</p> <p>Units: mm (inch) Tolerance: ± 0.25 (0.01)</p>
KA-3528LVSECKT-J4	AlGaInP	605	Water Clear	30	60	120°	
KA-3528LVSYCKT-J3	AlGaInP	590	Water Clear	20	30	120°	
KA-3528LVZGCKT	InGaIn	525	Water Clear	50	90	120°	
KA-3528LVWBS-D	InGaIn	470	Water Clear	30	45	120°	

LOW CURRENT SMD LED

Part Number	Material	λ_D (nm)	Lens Type	Iv (mcd) @2mA		Viewing Angle 2 θ 1/2	Dimensions			
				Min.	Typ.					
KPHB-1608LVCGKSURKC	AlGaInP	570	Water Clear	1.2	3	130°	<p>1.6mm x 0.8mm x 0.5mm (0603 Bi-Color)</p> <p>LED Chip</p> <p>Polarity mark</p> <p>Units: mm (inch) Tolerance: ± 0.15 (0.006)</p>			
	AlGaInP	630		2	8					
KPHB-1608LVZGKSURKC	InGaN	525	Water Clear	20	40	130°		<p>1.6mm x 1.25mm x 0.65mm (Bi-Color)</p> <p>LED Chip</p> <p>Polarity mark</p> <p>Units: mm (inch) Tolerance: ± 0.2 (0.008)</p>		
	AlGaInP	630		4	9					
KPTB-1612LVZGKSURKC	AlGaInP	630	Water Clear	4	9	150°			<p>2.0mm x 1.25mm x 0.45mm (0805 Super Thin, Bi-Color)</p> <p>LED Chip</p> <p>Polarity mark</p> <p>Units: mm (inch) Tolerance: ± 0.1 (0.004)</p>	
	AlGaInP	630		2	10					
KPHBM-2012LVZGKSURKC	AlGaInP	630	Water Clear	2	10	120°				<p>Other colour combinations are available upon request!</p>
	InGaN	525		50	90					

LOW CURRENT SMD LED

Part Number	Material	λ_D (nm)	Lens Type	Iv (mcd) @2mA		Viewing Angle	Dimensions
				Min.	Typ.		
KPBD-3224LVSURKCGKC	AlGaInP	630	Water Clear	10	30	20°	3.2mm x 2.4mm x 2.4mm (Dome Lens)
	AlGaInP	570		10	30		
KPBD-3224LVSURKZGKC	AlGaInP	630	Water Clear	10	30	20°	 Units: mm (inch) Tolerance: ± 0.1 (0.004)
	InGaN	525		120	250		

Other colour combinations are available upon request!



0201 PACKAGE – THE SMALLEST SMD-LED PACKAGE!

KPG-0603 SERIES

Features:

Dimensions: 0,65 mm x 0,35 mm x 0,2 mm

Wide viewing angle of 135° and 145°

High luminous intensity


Available colours = red, orange, green, yellow and blue

The 0201 package is suitable for mobile phones and portable electronic devices, digital cameras and camcorders, keyboards, loud speakers, head- and ear phones, microphones, hearing aids and medical devices. Especially for all applications in which the 0402 package is too large.




NEW SUPER-FLAT SMD-LED WITH 0,20 MM HEIGHT

KPG1-1608 SERIES



Features: Dimensions = 1,6 mm x 0,8 mm x 0,2 mm. Available in the colour red, orange, green, yellow and blue. Low power consumption



NEW DOME-LENS SMD-LED IN 0805 PACKAGE

KPTD-2012 SERIES

Features:

Dimensions = 2,0 mm x 1,25 mm, thickness = 1,05 mm

Available in the colours red, orange, green, yellow and blue

Applications:

Backlight, Status indicator, Home and smart appliances

Wearable and portable devices, Healthcare applications

