



A4 Technical Paper

FEATURES AND BENEFITS

- ISO 6 Cleanroom processed
- Excellent IPA resistant material
- · Compatible with most inks in writing without smearing
- Ultra low ionic contamination
- Ultra low particle and fiber generation
- Excellent heat resistant material for laser printing and photocopiers
- ROHS compliant
- Available sterile by Gamma Irradiation

APPLICATIONS

- Note taking
- Printing
- · Form & Logsheet



SPECIFICATIONS

CLEAROOM PAPER	(73 g/m²)
TESTING CONDITIONS	25°C, 55% RH

PARAMETERS	MEASUREMENT	STANDARD	TESTING VALUE	TESTING METHOD
Weight	g/m²	70±3.0	70.0	gsm
Width (CD)	mm	210mm±0.5mm	210	
Length (MD)	mm	297mm±0.5mm	297	
Thickness	μm	89±4	91.0	Micrometer
Bulk	cm³/g	1.24±0.1	1.25	
Smoothness (front side)	Sec	40±10	42↑	Bekk Type
Smoothness (Reverse side)	Sec	40±10	38↑	Bekk Type
Size degree	Sec	5 Sec↑	15	
Wet Tensile St.	MD	1.0↑	1.16	Horizontal Type
	CD	0.8↑	1	(Kg/15mm)
Dry Tensile St.	MD	6.0↑	7.90	
	CD	4.5↑	5.30	

PARTICLE DATA

PARTICE (DRY)	TESTING METHOD	TESTING RESULT	MEASUREMENT
≥0.3µm	IES-RP-CC003.3	221	count/ft ³
≥0.5µm	IES-RP-CC003.3	139	count/ft ³
≥1.0µm	IES-RP-CC003.3	82.4	count/ft ³

Call +44 (0) 1473 836205 Email info@integritycleanroom.com //integrity_eu in /company/integrity-cleanroom





IIMPORTANT NOTICE: This data sheet and its contents (the "Information") belong to Integrity" Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity* Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity® Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity® Čleanroom.

607-0001-TECHNICAL-PAPER.INDD | 6 FEBRUARY 2018 2:14 PM



PAGE 1































PRODUCT CODE	DESCRIPTION	COLOUR	GSM	SIZE	PACK SIZE
607-0005	Cleanroom Paper	White	73	A4	250 sheets
607-0001	Cleanroom Paper	Blue	73	A4	250 sheets
607-0002	Cleanroom Paper	Pink	73	A4	250 sheets
607-0003	Cleanroom Paper	Yellow	73	A4	250 sheets
607-0004	Cleanroom Paper	Green	73	A4	250 sheets
607-0007	Cleanroom Paper	White	72	A5	250 sheets

NOTE:

Call +44 (0) 1473 836205 Email info@integritycleanroom.com //integrity_eu in /company/integrity-cleanroom





IIMPORTANT NOTICE: This data sheet and its contents (the "Information") belong to Integrity" Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity* Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity® Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity® Čleanroom.

607-0001-TECHNICAL-PAPER.INDD | 6 FEBRUARY 2018 2:14 PM



PAGE 2

























^{*}Data shown are typical values and should not be used as specifications.