

| | | | | | | | | |
|--|-----------|-----------|--|-----|---------------------------|---------|-----|------|
| MATED WITH: PASSEND ZU: 2-964302-1 | LOC A1 | DIST — | REVISIONS ÄNDERUNGEN DESCRIPTION BESCHREIBUNG | | | DATE | DWN | APVD |
| PROJEKT NR.:B916106 | | | P | LTR | REVISED PER ECO-11-005150 | 21MAR11 | RK | HMR |

REFER TO PRODUCT GROUP DRAWING 1241437 FOR LATEST INFORMATION ON THE PART

RELEASED FOR PUBLICATION
FREI FÜR VERÖFFENTLICHUNG
ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG.


© COPYRIGHT — By —

| — | — | — | — | — | — | — | — |
|------------------|---------|------|------|----------|---------------|-------------|---|
| CUSTOMER PART NO | PART NO | REV. | PCS. | MATERIAL | SURFACE COLOR | DESCRIPTION | |

| | |
|---|---------|
| DIMENSIONS: DIMENSIONEN mm | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN | |
| ISO 8015 | — mh -E |
| ISO 2768 | — 140 |
| DIN 16901 | — 140 |
| 0 PLC | ± — |
| 1 PLC | ± — |
| 2 PLC | ± — |
| 3 PLC | ± — |
| 4 PLC | ± — |
| ANGLES/WINKEL | ± — |

| | |
|--|-----------|
| DWN | 16JUN1999 |
| CHK | — |
| APVD | — |
| PRODUCT SPEC PRODUKTSPEZ. | — |
| APPLICATION SPEC VERARBEITUNGSSPEZ. | — |
| WEIGHT GEWICHT | — |

| | | | |
|---|-----------|------------------------------|--------------------------|
| MATERIAL | — | FINISH OBERFLÄCHE/FARBE | — |
| TE | | TE Connectivity | |
| PART-NO. CROSS-REFERENCE INFO Teile-Nr. Zuweisungs-Information | | | |
| SIZE | CAGE CODE | DRAWING NO ZEICHNUNGS-NR. | RESTRICTED TO NUR FÜR |
| A4 | 00779 | C-1241396 | — |



| | | | | | |
|------------------------------------|-------------------|---|----------------|---------------|-----------|
| CUSTOMER DRAWING / KUNDENZEICHNUNG | SCALE MASSSTAB | — | SHEET BLATT | 1 OF VON 1 | REV A2 |
|------------------------------------|-------------------|---|----------------|---------------|-----------|