



BASIC DIMENSIONS FOR EVEN NO OF SPACES (SEE TABLE)
 BASIC DIMENSIONS FOR ODD NO OF SPACES (SEE TABLE)
 DETAIL R

- 1 CONTACT AREA PLATED WITH .000030 GOLD; SOLDER TAILS PLATED WITH .000150 TIN-LEAD, ALL OVER .000050 NICKEL
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 4 CONTACT AREA PLATED WITH .000030 GOLD; SOLDER TAILS PLATED WITH .000150 TIN, ALL OVER .000050 NICKEL.
- 5 FINISH: .000001 MIN. GOLD ON GOLD PLATED AREA, .000150-.000250 MATTE TIN LEAD ON TIN PLATE AREA, UNDER PLATING SHOULD BE .000050-.000100 NICKEL ON ENTIRE CONTACT.
- 6 FINISH: .000001 MIN GOLD ON GOLD PLATED AREA, .000150-.000250 MATTE TIN ON TIN PLATED AREA. UNDER PLATING TO BE .000050-.000100 NICKEL ON ENTIRE CONTACT
- 7 PRELIMINARY - NOT FOR PRODUCTION
- 8 SUPERSEDED
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	2.450	49	2.644	100	7-104076-8
	1.200	24	1.394	50	7-104076-7
	.700	14	.894	30	7-104076-6
	.200	4	.394	10	7-104076-5
	1.950	39	2.144	80	7-104076-4
	.950	19	1.144	40	7-104076-3
	1.450	29	1.644	60	7-104076-2
	.450	9	.644	20	7-104076-1
	2.450	49	2.644	100	5-104076-8
	1.200	24	1.394	50	5-104076-7
.700	14	.894	30	5-104076-6	
.200	4	.394	10	5-104076-5	
1.950	39	2.144	80	5-104076-4	
.950	19	1.144	40	5-104076-3	
1.450	29	1.644	60	5-104076-2	
.450	9	.644	20	5-104076-1	
FINISH	C	B	A	NO OF POS	PART NUMBER

5	2.450	49	2.644	100	2-104076-8
	1.200	24	1.394	50	2-104076-7
	.700	14	.894	30	2-104076-6
	.200	4	.394	10	2-104076-5
	1.950	39	2.144	80	2-104076-4
	.950	19	1.144	40	2-104076-3
	1.450	29	1.644	60	2-104076-2
	.450	9	.644	20	2-104076-1
	2.450	49	2.644	100	104076-8
	1.200	24	1.394	50	104076-7
.700	14	.894	30	104076-6	
.200	4	.394	10	104076-5	
1.950	39	2.144	80	104076-4	
.950	19	1.144	40	104076-3	
1.450	29	1.644	60	104076-2	
.450	9	.644	20	104076-1	
FINISH	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN K HELM 12-19-88	APVD R DURBIN 12-19-88	NAME
0 PLC ± -	1 PLC ± -	2 PLC ± -	3 PLC ± .005	4 PLC ± -
ANGLES ± -	SEE TABLE	SIZE	CAGE CODE	DRAWING NO
MATERIAL: HOUSING, THERMOPLASTIC COLOR-BLACK POST, COPPER ALLOY	FINISH	WEIGHT	A1 00779	104076

STE TE Connectivity
 HEADER ASSEMBLY, VERTICAL SHROUDED, WITH SLOT, AMPMODU System 50
 CUSTOMER DRAWING SCALE 4:1 SHEET 1 OF 1 REV U