





SPECIFICATION FOR APPROVAL

Customer		Cus# P/N	
P/N	SSC 33.5-20	DWG. NO.	
(1) Shape: 	A	33.50+/-1.00	m/m
	B	6.50+/-0.50	m/m
	C	20.00+/-0.60	m/m
	D	27.00+/-0.70	m/m
	E	1.40 +/-0.40	m/m
	F		m/m
	G		m/m
(2) Electrical Requirements: <p style="margin-left: 40px;">Z1= 37⁰ Ohms at 25 MHz</p> <p style="margin-left: 40px;">Z2= 85⁰ Ohms at 100 MHz</p>	(3) Test Conditions: a. Impedance Analyzer: HP-4191A b. Tesing Fixture: HP16092A c. Wire: 0.65 * 100mm * 2UEW 1Ts d. Drawing: 		
	(4) Packing:	(5) Appearance:	
(6) Remark: RoHs compliant	Approved:  Checked:  Drawn: 