


- NOTES
- ① CONTACT AREA:GOLD PLATING 0.2μm min.  
TERMINAL AREA:GOLD PLATING FLASH.  
UNDER PLATING:NICKEL 2μm min.
  - ② TOTAL LENGTH BECOMES 39.8±1 WHEN ③ IS SCREWED INTO ① COMPLETELY.
  - ③ THE RECOMMENDED CLAMP TORQUE OF REF.NO.⑨ TO BE 0.5N·m.  
LOCTITE 271, LOCPRIMER 7649, HENKEL JAPAN IS RECOMMENDED TO PREVENT REF.NO.⑨ FROM LOOSENING.  
SPACER FOR ASSEMBLY IS AVAILABLE HR30-8P-T02.  
TABLE FOR ASSEMBLY IS AVAILABLE HR30-7P-12SC-T01.
  - 4 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.

LIFE SIZE (1:1)



5	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0			
4	SILICONE RUBBER	(RED)	9	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0
3	COPPER ALLOY	①	8	POLYACETAL	NATURAL
2	COPPER ALLOY	①	7	CHLOROPRENE RUBBER	(BLACK)
1	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0	6	STAINLESS STEEL	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2:1	COUNT △	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
<b>HRS</b> HIROSE ELECTRIC CO., LTD.		APPROVED : MO. SATOH	07.03.05	DRAWING NO.	EDC3-113523-71		
		CHECED : EJ. KUNII	07.03.05	PART NO.	HR30-7P-12S(71)		
		DESIGNED : HS. KAWASHIMA	07.03.05	CODE NO.	CL130-0027-7-71		
		DRAWN : MK. SATO	07.03.02		△ 1/1		