


Aug.1.2016 Copyright 2016 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
1	DIS-C-000490	T.H	E.K	07.01.31					




- NOTES
- ① TOTAL LENGTH BECOMES 37.3 ± 1 WHEN ⑥ IS SCREWED INTO ① COMPLETELY.
 - ② APPLICABLE CRIMPING CONTACT: HR30-SC-211
(APPLICABLE WIRE: 26-30 AWG WIRE JACKET DIAMETER: $\phi 1$ MAX)
APPLICABLE CONTACT WITHDRAWAL: HP30-TP
 - ③ THE RECOMMENDED CLUMP TORQUE OF REF. NO. ⑥ TO BE $0.5N \cdot m$.
SPACER FOR ASSEMBLY IS AVAILABLE HR30-8P-T02.
STAND FOR ASSEMBLY IS AVAILABLE HR30-8J-12SC-T01.
 - ④ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

3	PBT	(BLACK)	UL94V-0	6	PPS	(BLACK)	UL94V-0
2	PPS	(BLACK)	UL94V-0	5	SYNTHETIC RUBBER	(BLACK)	
1	PPS	(BLACK)	UL94V-0	4	POLYACETAL	(NATURAL)	
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	E.KUNII	E.KUNII		M.SATO	
	'05.10.14	'05.10.14		'05.10.17	

 SCALE 5 : 1 UNITS mm	DRAWING NO. EDC3-112267-71 HRS HIROSE ELECTRIC CO., LTD	PART NO. HR30-8J-12SC(71) CODE NO. CL130-2016-1-71	1/1
-----------------------------------	---	---	-----



TO
R