


Aug.1.2016 Copyright 2016 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
2	DIS-C-000490	T.H.E.K		07.01.31					



- NOTES
- ① TOTAL LENGTH BECOMES 28.8±1 WHEN ⑥ IS SCREWED INTO ① COMPLETELY.
 - ② THE RECOMMENDED CLUMP TORQUE OF REF. NO.⑥ TO BE 0.5N·m.
LOCTITE 271, LOCPRIMER 7649, HENKEL JAPAN IS RECOMMENDED TO PREVENT REF. NO.⑥ FROM LOOSENING.
SPACER FOR ASSEMBLY IS AVAILABLE HR30-6P-T02.
 - ③ TABLE FOR ASSEMBLY AND SOLDERING IS AVAILABLE HR30-6R-6P-T01.
 - ④ SURFACE PLATING: GOLD PLATING 0.2μm min.
UNDER PLATING: NICKEL PLATING 2μm min.
 - ⑤ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
3	PPS	(BLACK) UL94V-0	6	PBT	(BLACK) UL94V-0
2	BRASS	④	5	CR	(BLACK)
1	PPS	(BLACK) UL94V-0	4	POLYACETAL	(NATURAL)

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	M.HANYU	H.NAGANO	E.KUNII	M.SATO	
	'05. 8. 8	'05. 8. 8	'05. 8. 10	'05. 8. 10	

DRAWING NO.	PART NO.
EDC3-112570-71	HR30-6JA-6P(71)
SCALE	UNITS
5 : 1	mm

CODE NO.	1/1
CL130-2018-7-71	

TO
R