




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	AUG02/13	L.CHAN
B	ADD TOLERANCE	AUG12/14	L.CHAN
C	CHANGE SHIELD'S MATERIAL PER ECN 160658	JUN 14/16	L.CHAN



RECOMMENDED P.C.B. LAYOUT  
(COMPONENT SIDE OF BOARD)



RECOMMENDED PANEL CUTOUT



**MATERIALS:**  
 PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC  
 FLAMMABILITY RATING UL 94V-0,  
 COLOUR: BLACK  
**CONTACTS:**  
 PHOSPHOR BRONZE  
 PLATING: 50 u " [1.27 MICRONS]  
 MIN. GOLD ON MATING SURFACES.  
 50 u " [1.27 MICRONS]  
 MIN. NICKEL UNDERPLATE  
 100 u " [2.54 MICRONS]  
 MIN. MATTE TIN ON CONTACT TAILS.  
**SHIELD:** STAINLESS STEEL WITH TIN DIP ON SOLDER TAIL.

PART NUMBER: RJHSE-5380-02

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE	DRAWN AMY.Z	DATE AUG02/14	Amphenol Canada Corp. www.amphenolcanada.com
PRIMARY UNITS INCH	CHECKED L.CHAN	DATE AUG02/14	
SECONDARY MILLIMETERS	M.E. APP'D		TITLE
REFERENCE IN PARENTHESES	Q.A. APP'D		2 PORT HIGH SPEED MODULAR JACK, 8P8C, SHIELDED, WITHOUT LED OPTIONS - RoHS COMPLIANT
GENERAL TOLERANCES	DWG APPR.		DWG. NO.
1 DECIMAL PLACE	ENG. REL. NO.		P-RJHSE-5380-02
2 DECIMAL PLACES ±0.020	REF.		REV
3 DECIMAL PLACES ±0.015	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	C
ANGULAR DEGREES ±1.0°			CODE ID NO. 03554 DWG SIZE: c SCALE: N/A SHEET 1 OF 1