


E type, Normal Key



Item	Part number	Cable OD Range
1	MA5CAE1700-S1	4.5-7.5 mm
2	MA5CAE1700-S2	7.5-11.0 mm
3	MA5CAE1700-S3	11.0-15.0 mm

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	FIRST RELEASE	Sep.07.2015	Drack	Tommy
A2	-	UPDATED COUPLING NUT	Oct.22.2015	Drack	Tommy

NOTES: UNLESS OTHERWISE SPECIFIED

- MATERIAL:  
INSULATION INSERT: PA66, UL94 V0  
SEAL: VITON, EPDM  
HOUSING BODY: ZINC DIE CAST, NICKEL PLATED  
COUPLING NUT: ZINC DIE CAST, NICKEL PLATED
- SPECIFICATIONS:  
2.1 CURRENT RATING: 9 AMPS  
2.2 VOLTAGE RATING: 125 V AC/DC  
2.3 OPERATING TEMPERATURE: -20°C TO +130°C  
2.4 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 2500 VOLTS AC.  
2.5 DEGREE OF PROTECTION: IP67 ( MATED CONDITION )  
2.6 DEGREE OF POLLUTION: 3 PER UL840  
2.7 OVERVOLTAGE CATEGORY: III PER UL840  
2.8 MATING CYCLE DURABILITY: >500 CYCLES  
2.9 ROHS COMPLIANT
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

QUANTITY	SEE PART NUMBER CHART	PART NUMBER	DESCRIPTION	ITEM

SIGNATURES		DATE	MATERIALS LIST	
DRAWN:	Dck	04/22/2015	<p><b>Amphenol</b></p> <p>Site Systems - <a href="http://www.amphenol-site.com">www.amphenol-site.com</a> 44724 Morley Drive Clifton Township, MI 48036</p>	
CHECKED:				
ENGINEER:				
APPROVAL:			M23A PLUG, STR. 17P, E TYPE, CHECKMATE	

UNLESS OTHERWISE SPECIFIED		PROCESS SPECIFICATIONS:		NEXT ASSY:	
1) All dimensions are in millimeters.		1) THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA ARE THE PROPERTY OF AMPHENOL CORPORATION. NO RIGHTS OR PERMISSIONS ARE GRANTED FOR REPRODUCTION OR MANUFACTURING VARIATIONS.		SCALE: NONE	
2) Tolerances are as follows: A: ±0.15 B: ±0.10 C: ±0.08		3) Note reference =		SIZE: B	
3) Note reference =		CUSTOMER:		TYPE: C-	
				DRAWING NO: MA5CAE1700-Sx	
				REVISION: A2	