


SIZE	PART NO.	REV.
B	2744555576	5



NOTES:

1. PACKING: PARTS ARE SUPPLIED BULKPACED 400 PCS/BG W/ A OXIDATION STRIP 1BG/BX 20BX/FZ=8K PCS/CT.
2. PARTS MEET FAIR-RITE PRODUCTS' VISUAL INSPECTION CRITERIA FOR GENERIC SURFACE MOUNT BEADS.
3. PART MEETS FAIR-RITE PRODUCTS' SOP ELC-27 FOR THERMAL SHOCK RESISTANCE.
4. IMPEDANCE MEASURED USING AN HP4191A ON A 16092A TEST FIXTURE.

A MAX	B	C	D
5.0	4.75/5.25	10.05/10.95	2.00/3.00
.197	.197	.413	.098

Bold dimensions are in millimeters,\* light dimensions are in inches for reference

Impedance (OHMS)	
25 MHz	100 MHz
340 MIN	480 MIN

5	B-305	CHANGE "C" DIMENSION	J.J.	3-21-01
4	9-1900	WIRE PART NUMBER ADDED	S.Z.	12-6-99
3	9-197	CHANGE BLANK FR#	S.Z.	2.10.99
2		UPDATED DIMENSIONS AND ELECTRICAL SPECS	K.R.	8-8-97
1		5.0 Max. WAS 4.9 Max.	D.S.	03.06.96
REV.	ECN	DESCRIPTION	DRFT	DATE

REVISIONS

APPLICABLE SPECS	DRAWING CLASS	C	FAIR-RITE PRODUCTS CORP.		
	MATERIAL	FR# 44	TITLE 2-1/2 TURN SM WIDE BAND CHOKE		
Tolerances Unless Otherwise Indicated	FINISH		DRAWN BY	DATE	SIZE PART NO.
3PL ±.005			D.A. SCHULZ	28.05.1996	B 2744555576
2PL ±.010			CHKD BY		REV. 5
FRACT ±1/64"			APPRVD BY		SCALE 3X SHEET 1 of 1
ANGLE ±1'					