

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	18SEP2017	YC	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:

INSULATION MATERIAL: PC

RATED VOLTAGE: 1000V

RATED CURRENT: 200A

INSULATION RESISTANCE: $\geq 400M\Omega$

RATED IMPULSE VOLTAGE: 8KV

POLLUTION DEGREE: 3

CONTACT RESISTANCE: $\leq 0.5m\Omega$

FLAMMABILITY: UL94V-0

MATING CYCLES: 500 CYCLES

WIRE RANGE: $25mm^2 \sim 70mm^2$

CONTACT TYPE: CRIMP TYPE.

注释:

1. 技术参数:

绝缘材料: PC

额定电压: 1000V

额定电流: 100A

绝缘电阻: $\geq 400M\Omega$

脉冲电压: 8KV

污染等级: 3

接触电阻: $\leq 0.5m\Omega$

阻燃等级: UL94V-0

插拔次数: 500次

接线范围: $25mm^2 \sim 70mm^2$

接线类型: 压接

T2111013101-007

HMN-001-MC

HMN-001 MALE MODULE INSERT, CRIMP
HMN-001 冷压模块公插

PART NUMBER

PART DESCRIPTION

料号

描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 18SEP2017

YORK CHEN

CHK 18SEP2017

GINO YAO

APVD 18SEP2017

CHRIS WANG

PRODUCT SPEC

108-137057

APPLICATION SPEC

114-137057

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

HMN-001-MC

SIZE

A3

CAGE CODE

00779

DRAWING NO

T2111013101007

RESTRICTED TO

-

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

-

FINISH

-

SCALE

1:1

SHEET

1 OF 1

REV

B

1470-19 (3/13)