

CUSTOMER TERMINAL RoHS LEAD(Pb)—FREE
Sn96%, Ag4% Yes Yes





CUSTOMER TO DETERMINE LAND LAYOUT



## ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

| PARAMETER       |     | TEST CONDITIONS    | VALUE              |
|-----------------|-----|--------------------|--------------------|
| D.C. RESISTANCE | 1-3 | @20°C              | 0.160 ohms max.    |
| D.C. RESISTANCE | 6-4 | @20°C              | 0.400 ohms max.    |
| INDUCTANCE      | 1-3 | 100kHz, 10mVAC, Ls | 370uH min.         |
| DIELECTRIC      | 1-6 | 6250Vrms, 1 second | 5000Vrms, 1 minute |
| TURNS RATIO     |     | (6-4):(1-3)        | 2:1, ±2%           |

## GENERAL SPECIFICATIONS:

6C) OPERATING TEMPERATURE RANGE: -40°C to +85°C.

CURRENT RATING: 1A

VOLTAGE-TIME: 20VuS for Unipolar operation 40VuS for Bipolar operation

SWITCHING FREQUENCY: 150kHz min.

68 11mm min. creepage and clearance between PRI & SEC.

COPLANARITY: All 6 terminals must lie on a plane within .004 [.10] of Surface A after lead tinning.

- $\bigcirc$  Designed to comply with the following requirements as defined by IEC60601-1(ed): Amendment 1:
  - Providing two means of Patient Protection up to a working voltage of 360VAC.
- © Complies with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:
  - Reinforced insulation for a primary circuit at a working voltage of 550VAC,
     Overvoltage Category II, Pollution Degree 2, up to 2km above sea level.

Designed to comply with the following requirements as defined by IEC60664-1:

- Reinforced insulation for a primary circuit at a working voltage of 400VAC, up to 2km above sea level.

- 60 Designed to comply with the following requirements as defined by IEC61010-1:
  - Reinforced insulation for a Line to neutral voltage up to 1000Vrms, Overvoltage Category II, up to 2km above sea level.
  - Reinforced insulation for a Line to neutral voltage up to 600Vrms, Overvoltage Category II, up to 5km above sea level.
- 6C Complies with the following requirements as defined by IEC62368-1, UL/CSA62368-1 and EN62368-1:

   Reinforced insulation for ES3, operating frequency above 30kHz, working voltage up to 550Vrms, 1600Vpeak, Overvoltage Category II, Pollution Degree II, and up to 2km above sea level.

Qualified to AEC-Q200.

| NUMBER      |  |  |  |
|-------------|--|--|--|
| E205930     |  |  |  |
| CA-10486-UL |  |  |  |
| CA-10485-UL |  |  |  |
|             |  |  |  |

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

## DETAILS SUBJECT TO CHANGE

REV. DATE Packaging Specifications
Method: Tape & Reel
PKG-1055
Www.we-online.com/midcom
GA 9/16 SEE REVISION SHEET FOR REVISION LEVEL

Tolerances unless otherwise specified:

Angles: ±1° Decimals: ±.005 [.13]

Fractions: ±1/64 Footprint: ±.005 [.13]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

## TRANSFORMER

eiSos p/n: **750316032** 



750316032

SPECIFICATION SHEET 1 OF 1