


USED ON -




CABLE BUNDLE MANAGEMENT SYSTEM							
REF	PART No.	NOM ID	MAX OD	MIN REC CABLE OD	MAX REC CABLE OD	M NOM (g/m)	REEL
CBMS-10-P	EG1595-000	10	32	5	25	2.900	200m
CBMS-20-P	EG1596-000	20	42	10	38	3.100	200m
CBMS-40-P	EG1598-000	40	58	20	52	3.700	180M

CBMS - 10 - X

PRODUCT DESCRIPTION _____
 SIZE (mm) _____
 MATERIAL _____
 P = PBT V0 NATO GREEN _____

CUSTOMER DRAWING

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE, IN ANY MANNER, WITHOUT THE EXPRESS WRITTEN AUTHORIZATION FROM TE. WWW.TE.COM

DWN N. NAGAR		08 JUN 2016		MATERIAL -		HEAT TREAT -	
CHK J. SEABOURNE		09 JUN 2016		 TE Connectivity			
APVD A. POOLE		09 JUN 2016					
NAME CABLE BUNDLING MANAGEMENT SYSTEM							
SCALE DNS		SIZE A2		DRAWING NO CBMSXX-X		SHEET 1 OF 1	
LTR		REVISION RECORD		DATE		DWN APVD	
A		INITIAL RELEASE		08 JUN 2016		NN AP	
DIMENSIONS MM		TOLERANCES UNLESS OTHERWISE SPECIFIED		0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.05 3 PLC ±0.005 4 PLC ±0.0005			
ANGLES		0° 30'		SURFACE TEXTURE 1.6			