


# **PRODUCT DATA DRAWING**







NOTES.

- 1.
- 2. 3.
- Sn63 SOLDER REQUIRED IN CROSS HATCHED AREAS AS SHOWN. NO SOLDER ALLOWED IN INTERFACE. SOLDER SPLASH ALLOWABLE ON THIS FACE. CONNECTOR MUST BE FLUSH TO BOARD FOR OPTIMAL RF PERFORMANCE. 4.
- PART TO BE SHIPPED WITH TAPE AND REEL. 5.

#### MATERIAL:

BODY:	STAINLESS STEEL PER AMS-5640 OR ASTM A582 ALLOY S30300, TYPE 303, CONDITION A.
CONTACT:	BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04


PTFE PER ASTM D1710, TYPE I, INSULATOR: GRADE 1, CLASS B

#### FINISH:

GOLD PER ASTM B488, TYPE II, CODE C, CLASS .76 (.00003" MIN), OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .00010" MIN. BODY & CONTACT:

### **PERFORMANCE:**


IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 40.0 GHz
INSUL. RES.:	5000 MEGOHMS, MIN.



		SV PART NUMBER		INTERFACE		
			1211-602	209	SMOOTH BORE	
			1211-60210		LIMITED DETENT	
			1211-602	211	FULL DETENT	
MATERIAL: SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0'	UNLESS OTHE	RWISE SPECIFIED	G		
FINISH: SEE NOTES	DECIMAL: X ±.030 .X*X ±.010 .XX ±.010 .XX ±.010	1) ALL DIMENSIONS ARE IN 2) ALL DIMENSIONS ARE AF 3) BREAK CORNERS & EDGI 4) CHAM. 1ST & LAST THRE	INCHES [MILLIMETERS] TER PLATING. ES .005 R. MAX.	www.svmicrowave.com		
SURFACE AREA: N/A	INTERPRET DIMENSIONS AND TOLERANCES	<ul> <li>(a) ITAM. TO EAST MILLADS.</li> <li>(b) SURFACE ROUGHNESS 63-MILLADS.</li> <li>(c) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R.</li> <li>(c) TI REMOVE ALL BURRS</li> </ul>		SMP MALE STRAIGHT PCB		
PROPRIETARY	PER ASME Y14.5M - 1994		571 0 1/00/00	-	EDGE MOUNT	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC.	THIRD ANGLE PROJECTION	DRAWN:	DTL 04/02/20	SIZE DWG. NO.	1011 00000 00011	
ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF		CHECKED:	STW 04/02/20	В	1211-60209-60211	
SV MICROWAVE, INC IS PROHIBITED.		APPROVED:	STW 04/02/20	SCALE: 16:1	SHEET 1 OF 2	

	REVISION HISTORY				
RE	V	DESCRIPTION	DATE	APPROVED	
-	1	NRN 44729	04/20	STW	
A	[	DCN 49919	06/20	STW	

## **RECOMMENDED PCB MECHANICAL FOOTPRINT**



MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: <u>+</u> 1/64 ANGULAR: X° <u>+</u> 1°0'	UNLESS OTHERWISE SPECIFIED	S		
FINISH:	SEE NOTES	DECIMAL: X ±.030 .XX ±.010	1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS.	www.svmicrowave.com		
SURFACE AF	<sup>rea:</sup> N/A	.XXX ±.005	<ul> <li>() SURFACE ROUGHNESS 63-MIL-STD-10.</li> <li>() DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN T.I.R.</li> <li>() REMOVE ALL BURRS</li> </ul>		ALE STRAIGHT PCB	
PROPRIETARY		PER ASME Y14.5M - 1994		EDGE MOUNT		
	ATION CONTAINED IN THIS DRAWING	THIRD ANGLE PROJECTION	DRAWN: SEE SHEET 1			
ANY REPROD	PROPERTY OF SV MICROWAVE, INC. UCTION IN PART OR AS A WHOLE E WRITTEN PERMISSION OF		CHECKED:	BIZE DWG. NO.	1211-60209-60211	
	VE, INC IS PROHIBITED.	$\Psi$ $\Box$	APPROVED:	SCALE: 16:1	SHEET 2 OF 2	

REVISION HISTORY					
REV	DESCRIPTION	DATE	APPROVED		
	SEE SHEET 1				