

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV DESCRIPTION		DATE	APPROVED
01 PRELIMINARY		08/20	BNK





MATERIAL:

BODY, INSERT & COUPLING NUT:

STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1;

OR ASTM A582 TYPE 303, COND. A

LOCK RING & CONTACT:

BERYLLIUM COPPER PER ASTM B196,

ALLOY No. UNS C17300, TD04

BEAD: ULTEM 1000 PER ASTM D5205

SILICONE RUBBER PER A-A-59588, CLASS 2B, GRADE 60/70 GASKET:

FINISH:

BODY, INSERT & COUPLING NUT:

PASSIVATED PER AMS-2700

GOLD PER ASTM B488, TYPE II, CONTACT:

CODE C, CLASS 1.27, OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 50.0 GHz

ATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0′	UNLESS OTHERWISE SPECIFIED	
NISH:	SEE NOTES	DECIMAL: X ±.030 .XX ±.010	1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX.	
JRFACE AR	^{EA:} N/A	.XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES	3) BREAK CORNERS & EDGES 005 R. MAX. 4) CHAM 151 & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA: S ON COMMON CENTERS TO BE CONCENTRIC WITHIN T.I.R.	TI
		PER ASME V14 5M - 1994	7) REMOVE ALL BURRS	

MATERIAL:	SEE NOTES
FINISH:	SEE NOTES
SURFACE AR	REA: N/A
	PROPRIETARY
IS THE SOLE F ANY REPRODU	TION CONTAINED IN THIS DRAW PROPERTY OF SV MICROWAVE, JCTION IN PART OR AS A WHOL

DIMENSIONS ARE IN INCHES TOLERANCES:		
 FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' +15'		
DECIMAL: .X ±.030 .XX ±.010 .XXX +.005		
INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		

PER ASME Y14.5M - 1994	1) KEWOVE ALL BURKS	
THIRD ANGLE PROJECTION	DRAWN:	KRR 08/06/20
	CHECKED:	BNK 08/06/20
Y U	APPROVED:	BNK 08/06/20

		MICROWAVE www.svmicrowave.com
--	--	-------------------------------

SYNAPSE MALE TO 1.85mm MALE ADAPTER

,	CIZE	DWG. NO.		
)	B	1180-6	3051	
) _	S	CALE: 7:1		SHEET 1 OF 1