


REV. W

DIMENSIONS ARE IN INCHES		TOLERANCES ARE:		TITLE:	DWG NO:
ONE PLACE DECIMALS ± .1	THREE PLACE DECIMALS ± .005	ANGLES ± 2°		DUAL ROW 2mm x 2mm ASSEMBLY	TLE-1XX-XX-X-DV-X
TWO PLACE DECIMALS ± .01	FOUR PLACE DECIMALS ± .0020				SHEET 1 OF 2



TLE-1XX-XX-X-DV-X

No OF POSITIONS
-02 THRU -50
(PER ROW)

LEAD STYLE
-01: SURFACE MOUNT
(USE C-101-01-X)

OPTION
-A: ALIGNMENT PIN (SEE FIG. 2 & 3, SHT. 2)
(USE TLE-XX-D-XX)
(MOLDED TO POSITION OR STAKED)
(SAMTEC DISCRETION WHICH -A PIN IS USED)
(MOLDED 3 POSITION MIN. SEE FIG. 2, SHT 2.)
(STAKED 4 POSITION MIN. SEE FIG. 3, SHT 2)
-P: PICK & PLACE PAD OPTION
(SEE FIG 4, SHT 2)
(USE MPP-03)
(4 POS. MIN.)
-TR: TAPE AND REEL OPTION
(AVAILABLE FOR 02 THROUGH 37 POSITIONS ONLY)
-K: POLYAMIDE FILM PAD (3 POS MIN)
(.005 [.13] THICKNESS WITH SILICONE ADHESIVE)
(SEE FIGURE 5, SHEET 2)

BODY SPECIFICATION

PLATING SPECIFICATION
-G: GOLD
.000010 GOLD ON ENTIRE CONTACT





FIG. 1

SECT. "A-A"

- NOTES:
1. MINIMUM PUSHOUT FORCE: .4 lb.
 2. COPLANARITY; POS -02 THRU -26: .004
POS -27 THRU -50: .006
 3. (C2) REPRESENTS A CRITICAL DIMENSION
 4. ALL POSITIONS TO BE PACKAGED IN TUBES.
 5. FOR EVERY FINISHED PART, ONE POSITION WILL BE LOST WHEN CUTTING BODY TO LENGTH.
 6. BURR ALLOWANCE: .003 [.08] MAX
 7. CUT FLASH TO BE .010 [.25] MAX WITH NO FLASH ALLOWED IN HOLES OR EXTENDING BELOW LEADS.

DO NOT SCALE FROM THIS PRINT.

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:
BODY:
VETRA E130I
COLOR:BLACK
TERMINAL:
PHOSPHER BRONZE

MISC\MKTG\TLE-MKT1

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: D PURVIS 01-20-97 TLE-1XX-XX-X-DV-X
SHEET 1 OF 2

PLOT SCALE 1=-.2