




used for: D-SUB

POS.	A -0.76	B -0.25	C	Part-No.
9	31.19	16.46	25.00 $+0.12$ -0.13	320X12519X
15	39.52	24.79	33.30 $+0.15$ -0.1	320X12539X
25	53.42	38.50	47.04 ± 0.13	320X10559X
37	69.70	54.96	63.50 ± 0.13	320X12559X



NOTES:

1. METALSHELLS: STEEL; min. 320 μ m TIN
2. INSULATORS: PBT GF UL 94 V-0, BLUE
3. CONTACTS: COPPER ALLOY,
- (b) 4. PLATING: GOLD FLASH over NICKEL
5. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
6. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC
- (b) 7. CURRENT RATING: 1,5 A
- (b) 8. OPERATING TEMPERATURE: $-25\text{ }^{\circ}\text{C} \dots +85\text{ }^{\circ}\text{C}$

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

tolerance			dim. in mm	
2006	date	name		
drawn	03.02.	Lehmenkühler		
appd.	03.02.	Mickenbecker		
norm	DIN 41652			
d-old				
3 x b	Ä21-0102	23.02.2022	ABU	
a	Original			
rev.	description	date	name	



scale:	2:1	
material:	SEE NOTES	
title:	D-SUB GENDER CHANGER 2 x SOCKET CONNECTOR 9-37pos.	
dwg no:	AutoCAD 2004	DIN-A
	16K1A1724	4
part no:	SEE TABLE	
		sh: 1/1