




1

2




3

4

REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
A	ECN2020072	NEW RELEASE	Staven 2020-09-03	Staven 2020-09-03	Biao 2020-09-03
B	ECN2022152	Update Comments	Abner 2022-09-28	Staven 2022-09-28	Sam 2022-09-28



PCB LAYOUT RECOMMEND  
(TOP VIEW) TOLERANCE: ±0.05



NOTES:

1. MATERIAL: SUS 304-H T=0.15mm;
2. BURR: 0.03mm MAX.
3. PLATING: Tin 80-160u" SURFACE PLATING OVER ALL, Ni 40-80u" UNDER PLATING OVER ALL.
4. The NEUTRAL SALT SPRAY TEST SHALL NOT RUST AT 24h;
5. WITH "▼" MUST BE CPK CONTROL.

UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		Amphenol AORORA	
X.	±0.30	X. '	± 5'			Amphenol Aorora Technology (Huizhou) Co.,Ltd	
X.X	±0.25	X.X '	± 4'				
X.XX	±0.20	X.XX '	± 3'	DOC TYPE: Customer Drw		TITLE: CLIP 4.5X2.2X2.3 GAP0.91 SMD	
X.XXX	±0.15	X.XXX '	± 2'	DRAWN DATE: Staven 2020-07-02	SIZE: A4		
LINEAR DIMS		ANGLES DIMS		DESIGN DATE: Staven 2020-07-02	PART NUMBER: Z02G-4G7R1-11000		
DWG NO.: A-S0609				CHECKED DATE: Biao 2020-07-02	REV. B		
MATERIAL: SEE NOTES		FINISHED: SEE NOTES		APPROVED DATE: Biao 2020-07-02	SCALE: 1:1	UNIT: mm	SHEET 1 OF 1



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AOR. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AOR. © 2019 AOR




1

2

3


4

REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
A	ECN20200072	INITIAL RELEASE	Staven 2020-09-03	Staven 2020-09-03	Biao 2020-09-03
B	ECN2022152	Update Comments	Abner 2022-09-28	Staven 2022-09-28	Biao 2022-09-28



NOTES:

- MATERIAL:
  - CARRY TAPE: HIPS, T=0.50mm, COLOR: TRANSPARENT.
  - REEL: HIPS, BLUE.
  - SHIM: PET, CLEAR.
  - Protective belt: PS, CLEAR.
- PRIMARY PACKING: 4500PCS/REEL.
- SECONDARY PACKING: 15 REELS/CARTON  
("TOTAL"=15\*4500/CARTON).
- PEELING RESISTANCE: 0.2N~1.2N(20~120gf);  
PEELING ANGLE: 165°~180°;  
PEELING SPEED: 300mm/minutes.



UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		 Amphenol Aorora Technology (Huizhou) Co.,Ltd
X.	±0.38	X. °	± 3'			
X.X	±0.36	X.X °	± 2'			
X.XX	±0.25	X.XX °	± 1'	DOC TYPE: Packing Drw		<b>SIZE:</b> A4 <b>PART NUMBER:</b> 202G-4G7R1-11000
X.XXX	±0.15	X.XXX °	± 1'	DRAWN DATE: Staven 2020-07-02	CHECKED DATE: Biao 2020-07-02	
LINEAR DIMS	ANGLES DIMS			DESIGN DATE: Staven 2020-07-02	APPROVED DATE: Biao 2020-07-02	<b>SCALE:</b> 1:1 <b>UNIT:</b> mm <b>SHEET:</b> 1 OF 1
DWG NO.:	A-HO339					
MATERIAL	SEE NOTES					
FINISHED	SEE NOTES					