



REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
D	PRODUCT DWG - REV PER EAR 14897	FEB04/22	S.M.
E	PRODUCT DWG - REV PER EAR 14897	JUN09/22	S.M.



NOTES:

- FOR USE WITH AMPHENOL FLH CRIMP CONTACTS:
 - FLH-PC136-T01 OR FLH-PC136-1-T01
 - FLH-SC136-T01 OR FLH-SC136-1-T01
- WIRES: 22 - 18 AWG (1.5 TO 1.8 mm INSULATION DIA)

OPERATION INSTRUCTIONS

PLEASE REFER TO APPLICATION SPECIFICATION NO. S6202C

AMPHENOL PART NUMBER: FLH-CT-0-03



UNLESS SPECIFIED OTHERWISE	DRAWN	I.NELSON	JUN04/21
PRIMARY UNITS MILLIMETRES	CHECKED	S.MUGAN	JUL12/21
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.		
2 DECIMAL PLACES	REF.	EAR 14987	
3 DECIMAL PLACES	THIRD ANGLE PROJECTION		
ANGULAR DEGREES	DO NOT SCALE DRAWING		

Amphenol Canada Corp.
Commercial Products

FLH CRIMP TOOL
RoHS COMPLIANT

DWG. NO. **P-FLH-CT-0-03**

CODE ID NO. **03554** | DWG SIZE: X | SCALE: 1:1 | SHEET 1 OF 1