

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91 929



SWITCH - BASIC

CATALOG LISTING

V7-1B17D8-122

CW-B2036

CATALOG LISTING
V7-1B17D8-122
PAGE 1 OF 1
RELEASE NO. PR-23344
REPLACES
ISSUE
M
2




REVISIONS
A REL PR23344
DCS 12 FEB 98

CHECK
12 FEB 98
CHECK

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ± .030 TWO PLACE (.00) ± .015 THREE PLACE (.000) ± .005 ANGLES ± WEIGHT	
OPERATING FORCE — — — 43 GRAMS MAX RELEASE FORCE — — — 4 GRAMS MIN DIFFERENTIAL TRAVEL — — — .053 MAX OVERTRAVEL — — — — .118 MIN RELEASE TRAVEL — — — — .032 MIN	CONTACT ARRANGEMENT S P D T L156 11A 1/3HP 125, 250 OR 277 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L"		



DDM/CAD
DRAWN
DCS 30 JAN 98
CHECK