


MA 2,5/5.SNBTA


Spacing 5 mm (.200")



5 mm block - Switch connection by short blade - Equipped with two test sockets DIA. 2,3 mm / .090"

M 4/6.SNBT...


Spacing 6 mm + 0,05 (.238")



6 mm block - Switch connection by short blade - Equipped with two test sockets DIA. 2 mm / .079"

M 4/6.SNB

Spacing 6 mm + 0,05 (.238")



6 mm block - Switch connection by long blade



Color	Type	Part numbers
Grey / Grey	MA 2,5/5.SNBTA	0115 505.16



Color	Type	Part numbers
Grey / Grey	M 4/6.SNBT1	0115 438.12
Grey / Beige V0	M 4/6.SNBT2	0115 441.15



Color	Type	Part numbers
Grey / Grey	M 4/6.SNB	0115 686.13
Orange/Orange	M 4/6.SNB	0105 053.22
Beige V0/Beige	M 4/6.SNB.V0	0195 686.14

Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
Compression Solid wire	0,5-4 mm ²		24-12 AWG	24-12 AWG
clamp Stranded wire	0,5-4 mm ²		24-12 AWG	24-12 AWG

Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
Compression Solid wire	0,5-4 mm ²		22-10 AWG	
clamp Stranded wire	0,5-4 mm ²		22-10 AWG	

Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
Compression Solid wire	0,5-4 mm ²		22-10 AWG	20-12 AWG
clamp Stranded wire	0,5-2,5 mm ²		22-10 AWG	20-12 AWG

Voltage

Rated	320 V	600 V	150 V
Pulse	4 kV		
Pollution degree	3		

Voltage

Rated	320 V	300 V
Pulse	4 kV	
Pollution degree	3	

Voltage

Rated	400 V	300 V	300 V
Pulse	4 kV		
Pollution degree	3		

Current

Rated	10 A	15 A	10 A
-------	------	------	------

Current

Rated	10 A	10 A
-------	------	------

Current

Rated	10 A	10 A	10 A
-------	------	------	------

Wire size

Rated / Gauge	4 mm ² / A3	12 AWG	12 AWG
Wire stripping length	Recomm. screwdriver	Recomm. torque	Protection
10 mm .39"	3,5 mm .16"	0,4-0,6 Nm 3,5-5,3 lb.in	IP 20 NEMA 1

Wire size

Rated / Gauge	4 mm ² / A4	10 AWG	
Wire stripping length	Recomm. screwdriver	Recomm. torque	Protection
9,5 mm .374"	4 mm .157"	0,5-0,6 Nm 4,4-5,3 lb.in	IP 20 NEMA 1

Wire size

Rated / Gauge	2,5 mm ² / A4	10 AWG	12 AWG
Wire stripping length	Recomm. screwdriver	Recomm. torque	Protection
9,5 mm .37"	4 mm .16"	0,5-0,6 Nm 4,4-5,3 lb.in	IP 20 NEMA 1

Type	Part numbers
FEM6	th. 2,8 mm 0118 368.16
SCF6	th. 3,0 mm 0118 707.03
SCF6	th. 3,0 mm 0128 707.05
SCF6 V0	th. 3,0 mm 0198 707.04
SCFM6	th. 3,0 mm 0114 825.05
SCFEX1 (1)	th. 2,4 mm 0103 619.04
SCFEX3 (1)	th. 2,4 mm 0103 620.01
CBM5	th. 0,5 mm 0178 745.14
CBM8	th. 0,8 mm 0178 746.15

Type	Part numbers
FEM62	th. 3 mm 0114 994.07
SCFM6	th. 3 mm 0114 825.05
SCFEX1 (1)	th. 2,4 mm 0103 619.04
SCFEX3 (1)	th. 2,4 mm 0103 620.01
FC2	DIA. 2 mm 0007 865.26
CBM5	th. 0,5 mm 0178 745.14
CBM8	th. 0,8 mm 0178 746.15
PC61	10 poles 0163 311.22
AD2,5	0114 205.20

Type	Part numbers
FEM62	th. 3 mm 0114 994.07
FEM62	th. 3 mm 0103 612.25
FEM62 V0	th. 3 mm 0194 994.00
SCFM6	th. 3 mm 0114 825.05
SCFEX1 (1)	th. 2,4 mm 0103 619.04
SCFEX3 (1)	th. 2,4 mm 0103 620.01
FC2	DIA. 2 mm 0007 865.26
CBM5	th. 0,5 mm 0178 745.14
CBM8	th. 0,8 mm 0178 746.15
PC61	10 poles 0163 311.22
AD2,5	0114 205.20
DCJ	yellow 0173 059.03

(10) Sides of block (6) RC510 on blade
Note : (1) End sections and separators snapped on rails.

(11) Sides of block (6) RC810 on blade

(11) Sides of block