

# tesa® 62936

Double-sided PE foam mounting tape

## PRODUCT INFORMATION

### **Product Description**

tesa® 62936 is a double-sided PE-foam tape for constructive mounting applications. It consists of a highly conformable PE-foam backing with a tackified acrylic adhesive.

#### Product benefits:

- Versatile adhesive for high immediate adhesion on numerous substrates
- High ultimate adhesion level for a secure bonding performance
- UV, water and ageing resistant
- Compensates for differing thermal expansion of dissimilar materials
- · High immediate bonding strength even at low bonding pressure
- Very good cold shock absorbtion

## **Main Application**

- Interior wall cladding panels
- Bumper rails on commercial freezers
- · Injection moulded plastic parts
- · Mirrors and coloured glass panels

## **Technical Data**

<ul><li>Backing material</li><li>Colour</li><li>Total thickness</li></ul>	PE foam black/white 1600 µm	<ul><li>Type of adhesive</li><li>Elongation at break</li><li>Tensile strength</li></ul>	tackified acrylic 200 % 19 N/cm
		ŭ	

# Adhesion to

Steel (initial)  ABS (initial)  Aluminium (initial)	16.0 N/cm 17.0 N/cm 15.0 N/cm	<ul><li>Steel (after 14 days)</li><li>ABS (after 14 days)</li><li>Aluminium (after 14 days)</li></ul>	19.0 N/cm 19.0 N/cm 19.0 N/cm
PC (initial)	19.0 N/cm	PC (after 14 days)	19.0 N/cm
PET (initial)  PET (initial)	2.0 N/cm 15.0 N/cm	PE (after 14 days)  PET (after 14 days)	3.0 N/cm 19.0 N/cm
PP (initial) PS (initial)	3.0 N/cm 19.0 N/cm	<ul><li>PP (after 14 days)</li><li>PS (after 14 days)</li></ul>	7.0 N/cm 19.0 N/cm
PVC (initial)	19.0 N/cm	PVC (after 14 days)	19.0 N/cm

Page 1 of 2 / As of 05/20/10

#### tesa UK Ltd.



# tesa® 62936

Double-sided PE foam mounting tape

## PRODUCT INFORMATION

### **Properties**

- Static shear resistance at 23°C Humidity resistance Static shear resistance at 40°C ■ Temperature resistance short term 80 °C ■ Temperature resistance long term 80 °C
- Resistance to chemicals Softener resistance
- ++ Evaluation across relevant tesa® assortment: ++ very good, + good, o medium, - low

#### **Additional Info**

Ageing resistance (UV)

Liner variants:

PV0 brown glassine paper (71 µm) PV14 white PE-coated paper (120  $\mu$ m) PV10 red filmic liner (120 µm)

tesa® 62936 has been tested by TÜV Rheinland, Germany. The test confirms the longterm adhesion performance after IEC 61215 / 61646 climate tests and a 85°C temperature resistance. (TÜV report number 21209595).

#### Peel Adhesion:

- immediate: foam splitting on PC, PS, PVC
- after 14 days: foam splitting on Steel, Aluminium, ABS, PC, PS, PET, PVC

Page 2 of 2 / As of 05/20/10