



- Adjustable and pre-set relative humidity
- Optical operating display (LED)
- High switching capacity
- Clip fixing
- Temperature-compensated

The electronic hygrostat senses the relative humidity in an enclosure with electric/electronic components, and turns on a heater at the set point, helping prevent the formation of condensation in the enclosure. The LED integrated in the adjustment knob is lit when the connected heater is in operation.










## Technical Data

Switch difference	5% RH (± 3% RH tolerance) at 25°C/77°F (50% RH)		
Reaction time	5 sec.		
Contact type	change-over contact (relay)		
Service life	> 50,000 cycles		
Max. switching capacity (relay	240VAC, 8 (1.6) A		
output)	120VAC, 8 (1.6) A		
	24VDC, 4A		
Optical indicator	LED		
Connection	5-pole terminal, clamping torque 0.5Nm max.:		
	rigid wire 2.5mm²		
	stranded wire (with wire end ferrule) 1.5mm <sup>2</sup>		
Mounting	clip for 35mm DIN rail, EN60715		
Casing	plastic according to UL94 V-0, light grey		
Dimensions	64.5 x 42 x 38mm		
Weight	approx. 70g		
Fitting position	vertical		
i ittilig position	Voltical		
Operating / Storage temperature	0 to +60°C (+32 to +140°F) / -20 to +70°C (-4 to +158°F)		
	11		










Connection diagram



Example of connection

Art. No.	Operating voltage	Setting range	Approvals
01245.0-00 🕸	230VAC, 50/60Hz	40 to 90% RH	VDE + CSA-US
01246.0-00	230VAC, 50/60Hz	65% RH pre-set	VDE + CSA-US
01245.9-00	120VAC, 50/60Hz	40 to 90% RH	CSA-US
01246.9-00	120VAC, 50/60Hz	65% RH pre-set	CSA-US