

TrueNet®

Tool and Punchdown Pad



The TrueNet® Tool guarantees strong, reliable and consistent wire terminations in ADC KRONE Contacts (IDCs).

The new tool has been designed specifically to work with the smaller form factor IDC contacts that are used in the new Category 6 and 6_A jacks.

This tool is backwards compatible with all ADC KRONE LSA PLUS® IDCs including jacks and will replace the existing tool for all datacommunication products.

A core feature of the tool is the scissor action that cuts the wire, ensuring a clean and tidy termination of the wires. The tool also comes complete with two additional features, a wire removal hook and a flat blade screwdriver.

As density increases in the Data Centre RJ45 technologies get smaller, as an aid to these smaller RJ45's connectors ADC KRONE has developed the Punchdown Pad to help the termination process. The Punchdown Pad supports both new in-line and right angle small form factor Category 6 and 6_A jacks.

The tool and pad can be purchased separately or as part of a pack.

Features

- Compatible with LSA-PLUS® contacts and a range of other IDC technologies
- Scissor cutting action
- Wire removal hook
- Flat screwdriver blade
- Best practice aids

Benefits

- Suitable for use in all copper TrueNet® connectors and panels
- Rapid and reliable punch down performance
- Punchdown Pad promotes best termination practice
- Ensures strong and reliable terminations

TECHNICAL DATA



Technical Assistance:
Europe & Middle East
+32 2 712 6542
euro.tac@adckrone.com
www.adckrone.com

South Africa
+27 11 466 3333
infos@adckrone.com

United Kingdom
0800 960236
contactuk@adckrone.com

Ordering Information

Description	Catalogue number
TrueNet® Tool and Punchdown Pad*	6537 1 600-00
TrueNet® Tool (Pack of 1)	6537 1 500-00
TrueNet® Punchdown Pad Black (Pack of 10)*	6537 1 610-00

* Punchdown Pad Compatibility

Modular Jack, Category 6 KM8 Punchdown UTP	6830 1 830-0x
Modular Jack, Category 6 _A Punchdown UTP	6830 1 885-0x
Modular Jack, Category 6 RA Punchdown	6830 1 900-0x
Modular Jack, Category 6 _A RA Punchdown	6830 1 985-0x

Technical Specifications

Conductor Range	0.35 - 0.9mm
Insulation Range	0.7 - 2.6mm

Service Life

0.4mm wire	200,000 terminations
0.6mm wire	100,000 terminations
0.8mm wire	50,000 terminations

TECHNICAL DATA



Web Site: www.adckrone.com/en

UK Office: ADC Communications (UK) Ltd., Runnings Road, Kingsditch Trading Estate, Cheltenham, Gloucestershire GL51 9NQ, United Kingdom • Phone: +44 (0) 1242 264 400 Fax: +44 (0) 1242 264 488 Email: contactuk@adckrone.com

South African Office: ADC Telecommunications (Africa) PTY Ltd., 16 Brand Hatch Close, Kyalami Business Park, Midrand, 1685 Johannesburg, South Africa • Phone: +27 11 466 3333 Fax: +27 11 466 3300 Email: infos@adckrone.com

EMEA Office: ADC GmbH, Beeskowdamm, 3-11, 14167 Berlin, Germany • Phone: +49 308 453 1818 Fax: +49 308 453 1703. For a listing of all ADC KRONE's global sales office locations, please refer to our web site.

Specifications published here are current as of the date of publication of this document. Because we are continuously improving our products, ADC KRONE reserves the right to change specifications without prior notice. At any time, you may verify product specifications by contacting ADC GmbH headquarters in Berlin. ADC Telecommunications, Inc. views its patent portfolio as an important corporate asset and vigorously enforces its patents.

201054BE July 09 Original © 2009 ADC Communications (UK) Ltd. All Rights Reserved