SUNON

SPECIFICATION FOR APPROVAL

CUSTOMER

DESCRIPTION

AXIAL AC FAN

DIMENSIONS

Ø254X89 mm

MODEL

A2259-MBT

P/N

TC.GN

SUNON SPEC. NO. :

A25000260G-00

APPROVAL NO.

APPROVED BY

(AUTHORIZED)

						SPEC.NO	A25000260G-00
	_1				1	ISSUE DATE	09.21.2005
DRAWN	Anne 9/21	CHECKED	Lady %	APPROVED		EDITION	0
	3/21		150		N Who	REVISION DATE	
						E.SPEC	EA25012

|建準電機工業股份有限公司


SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD. 12FL., 120 CHUNG CHENG 1ST RD.,

KAOHSIUNG, TAIWAN, R. O. C.

TEL:886-7-7163069(41 LINES)

FAX:886-7-7163086~89





建準電機工業股份有限公司
SUNONWEALTH ELECTRIC
MACHINE INDUSTRY CO., LTD.

	SPEC.NO	A25000260G-00	REVISION	DA	TE.		-	10 F1	1
	ISSUE DATE	09. 21. 2005	EDITI	O	Ň	0	%	品, 3	2
	PAGE	2 OF 11		1	. 2	94.	10.	12	L
_						3.		جائب ا	J

医工業人

AXIAL AC FAN

MODEL: A2259-MBT

P/N: TC.GN

CHARACTERISTICS

1. Motor Design : Reliable Alveolate Motor Construction.

2. Insulation Resistance : 500 Megohms minimum at 500 VDC.

3. Dielectric Strength : 1800 VAC for one second.

4. Motor Protection : Thermal protected.

5. Noise Level : Measured in a semi-anechoic chamber

with background noise level below 15

dB(A). The fan is running in free air with the

microphone at a distance of one meter

from the fan intake.

6. Tolerance : ±15% on rated power and current.

7. Air Performance : Measured by a double chamber. The values

are recorded when the fan speed has stabilized

at rated voltage.

建準電機工業股份有限公司	SPEC.NO	A250002
SUNONWEALTH ELECTRIC	ISSUE DATE	09. 21.
MACHINE INDUSTRY CO., LTD.	PAGE	3 OF

			1/10	孤工業	(A)
EC.NO	A25000260G-00	REVISION DA	ATE	T 25	471
SUE DATE	09. 21. 2005	EDITIO	N 1	77 78	40
PAGE	3 OF 11			<i>9</i> 4. TU	. 12
			一彩	行	

SPECIFICATIONS

MODEL: A2259-MBT

P/N : TC.GN

1-1. Rated Voltage

: 220-240 VAC 50/60 Hz

1-2. Operating Voltage Range

: 150-250 VAC

1-3. Starting Voltage

: 150 VAC (25 deg. C POWER ON/OFF)

1-4. Rated Speed

: 1400/1600 RPM ± 10%

1-5. Air Delivery

: 600/665 CFM

1-6. Static Pressure

: 0.27/0.36 Inch-H₂O

1-7. Rated Current

: 0.15/0.13 AMP

1-8. Rated Power

: 30/30 WATTS

1-9. Noise Level

 $: 50/52 \, dB(A)$

1-10. Direction of Rotation

: Counter-clockwise viewed from front of fan blade

1-11. Operating Temperature

: -10 to +70 deg. C

1-12. Storage Temperature

: -40 to +70 deg. C

1-13. Bearing System

: Precision ball bearing system

1-14. Weight

: 2000 g

1-15. Safety

: UL/CUR/TUV/CE Approvals

1-16. Vibration

: Vibration of acceleration 1.5G and frequency 5~50~5Hz is applied in all

3 directions(X,Y,Z), in cycles of 1 minute each,

for a total vibration time of 30 minutes.

建準電機工業股份有限公司
SUNONWEALTH ELECTRIC
MACHINE INDUSTRY CO., LTD.


		/
SPEC.NO	A25000260G-00	REVISION DATE
ISSUE DATE	09. 21. 2005	EDITION
PAGE	4 OF 11	

MODEL: A2259-MBT

P/N : TC.GN

PERFORMANCE CURVES

STATIC PRESSURE



建準電機工業股份有限公司	SPEC.NO	A25000260G-00	REVISIO	N DA	TE	THE REAL PROPERTY.	一木	(AD)
SUNONWEALTH ELECTRIC	ISSUE DATE	09. 21. 2005	EDIT	ΙΟ	N	研	發	部
MACHINE INDUSTRY CO., LTD.	PAGE	5 OF 11				94.	10.	12

發行章

MATERIAL

2. Material

2-1. Frame


DIE-CAST ALUMINUM

2-2. Impeller

•

PC of UL 94V-0

DIMENSIONS




Air Flow Direction: Toward label side.

建準電機工業股份有限公司	Ŀ
SUNONWEALTH ELECTRIC	
MACHINE INDUSTRY CO., LTD.	ſ


			UNITS:	mm東工業保
	SPEC.NO	A25000260G-00	REVISION DA	不
	ISSUE DATE	09. 21. 2005	EDITIO	N 04 10 12
•	PAGE	6 OF 11		34. 10. 12

Alveolate Motor



Thermal Cutout

With Capacitor



建準電機工業股份有限公司			
SUNONWEALTH ELECTRIC			
MACHINE INDUSTRY CO., LTD.			

l	SPEC.NO	A25000260G-00	REVISION DAT
	ISSUE DATE	09. 21. 2005	EDITION
ſ	PAGE	7 OF 11	

Notes

I . Safety

- 1.SUNON will not guarantee this product if your application exceeds the limitations outlined in this specification.
- 2. There is no thermo-protector installed in this product, such as thermo-fuse, or current-fuse or thermo-protector. There may be smoking, ignition, or electric shock by insulation degradation in cases of motor lock, motor lead short circuit, overload, over voltage, and/or other failure. Please add the protection circuit to your product.
- 3. There is no reverse-connection prevention diode of VDC (+) and GND (-) installed in this product. Therefore, if VDC(+) and GND(-) are reverse connected, it may cause smoking, ignition, and/or destruction, although these conditions may not manifest immediately. We recommend that a protection device be installed on your product when there is a possibility of reverse-connection.
- 4. Please verify that this product is being installed and used in compliance with all safety standards. Please inform SUNON of any safety concerns prior to releasing your product to production.
- 5. Please handle and install this product carefully. Hitting or dropping this product may cause damage.
- 6.Please do not damage this product including coil and lead wires while installing or wiring. There may be smoking or fire.

建準電機工	業股份有限公司
SUNONWI	EALTH ELECTRIC
MACHINE	INDUSTRY CO., LTD.

			S. 75%
SPEC.NO	A25000260G-00	REVISION DATE	402
ISSUE DATE	09. 21. 2005	EDITION	10
P A G E	8 OF 11		94.
		7	4

Notes

- ${\rm I\hspace{-.1em}I}$. Specification modification
 - 1.SUNON offers engineering assistance on fan installation and cooling system design.
 - 2. Any change to the parameters specified in this document will be determined by mutual agreement between both parties. Parameters which are not specified in this specification will be identical to the final sample which has been approved by your company.
 - 3. Product will be shipped in accordance with this specification unless Sunon has been previously notified of parameters requiring exception.
 - 4. Parameters modified by mutual consent will be incorporated in this specification.
 - 5.Please notify SUNON in advance of any modification to your product or new application for this fan which may require a review of this specification.

建準電機工業股份有限公司	SPEC.NO	A25000260G-00	RE	VI	SI	ON	D.	AT		194	(A)
SUNONWEALTH ELECTRIC	ISSUE DATE	09. 21. 2005	E l) I	T	Ι	0	No	40	一發	部,
MACHINE INDUSTRY CO., LTD.	PAGE	9 OF 11							94	4. 10	. 12

發行章

Notes

III. Other

- 1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 2.Fan holders or bearings may be damaged if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits. Please handle this product carefully.
- 3.Please avoid operating SUNON's product in poisonous material (organic silicon, cyanogens, formalin, phenol, etc.) or corrosive gas environments (H2S, SO2, NO2, Cl2, etc).
- 4.SUNON does not warrant performance safety against accidents caused by dust, water, droplets, dew, bugs, etc.
- 5. Please advise us in advance if you require documents for export.
- 6.Improper mounting may cause harsh resonance, vibration, and noise. Please mount securely.
- 7. Safety is a top priority. Please furnish guard accessories to prevent injury to personnel.
- 8.Unless otherwise noted, all tests are conducted at 25°C ambient temperature and 65% relative humidity.
- 9. Always ensure that fans are stored according to the storage temperatures specified. Do not store in a high humidity environment. If the fans are stored for more than 6 months, SUNON recommends functional testing before using.
- 10.SUNON reserves the right to use components with equivalent specifications from multiple sources.

建準電機工業股份有限公司	SPEC.NO	A25000260G-00	REV	ISIOI	N D.	ATE	N. POR		(A)
SUNONWEALTH ELECTRIC	ISSUE DATE	09. 21. 2005	E D	ΙΤΙ	0		40	發	部,
MACHINE INDUSTRY CO., LTD.	PAGE	10 OF 11					94.	. 10.	12

Declaration of RoHS

Control declaration of environment- related substances/ materials

1.In accordance with the Restriction of Hazardous Substances (RoHS) Directive, Sunon product with P/N: GN models have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

No		Substance	Criteria
1	Halogens & its compounds (Su	Forbidden	
2	Chlorinated Organic Solvent		Forbidden
		Plastic (Frame, Impeller, wire harness, etc.)	<100ppm
		Solder	<1000ppm
3	Lead and its compounds	Iron Alloy	<3500ppm
		Aluminium Alloy	<4000ppm
		Copper Alloy	<4wt%
		Solder	<20ppm
4	Cadmium and its compounds	Cadmium Alloy	<100ppm
		Plastic	<5ppm
5	PBB and PBDE Category		Forbidden
6	PCB and PCT Category		Forbidden
7	СР		Forbidden
8	Mirex		Forbidden
9	PCN category		Forbidden
10	Hexavalent Chromium Compo	ounds	<100ppm
11	Mercury and its compounds		Forbidden
12	Asbestos		Forbidden
13	Organic Tin Compounds		Forbidden
14	Azo Compounds		Forbidden

建準電機工業股份有限公司SPEC.NOA25000260G-00REVISION DATESUNONWEALTH ELECTRICISSUE DATE09. 21. 2005E D I T I O N OF TO THE SUN DATE		BIE
SUNONWEALTH ELECTRIC ISSUEDATE 00 21 2005 F.D.I.T.L.O. & A. &	建準電機工業股份有限公司	DATE
SONOTWEALTH ELECTRIC ISSUE DATE 07.21.2003 E D 1 1 1 0 W	SUNONWEALTH ELECTRIC	0 例 研發部
MACHINE INDUSTRY CO., LTD. PAGE 11 OF 11 94. 10	MACHINE INDUSTRY CO., LTD.	94. 10. 12

發行章