

For more Information
please call

1-800-Belden1



Description:

RG-8/U type, 10 AWG stranded (7x19) .108" bare copper conductor, gas-injected foam HDPE insulation, Duobond II® + tinned copper braid shield (95% coverage), Belflex® jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	10	7x19	BC - Bare Copper	2.7432

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	7.239

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Belflex®	PVC Blend - Polyvinyl Chloride Blend

Overall Cabling

Overall Nominal Diameter: 10.287 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +80°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 139.891 Kg/Km

Max. Recommended Pulling Tension: 934.122 N

Min. Bend Radius (Install)/Minor Axis: 76.200 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

RG Type: 8/U

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Aerial: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

52

Nom. Inductance:

Inductance (µH/m)

0.193579

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

73.8225

Nominal Velocity of Propagation:

VP (%)

85

Nominal Delay:

Delay (ns/m)

3.9372

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

3.6091

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

5.9058

Maximum VSWR:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Max. VSWR
		5	2250	1.43:1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
10	1.9686
50	3.6091
100	4.9215
200	6.562
400	9.843
700	13.124
900	15.4207
1000	16.405
2000	24.6075
2250	26.248
3000	32.1538
4000	39.7001

Nom. Power Rating:

Freq. (MHz)	Rating (W)
5	3217
10	2681
50	1463

100	1073
200	805
400	575
700	424
900	366
1000	350
1500	278
1800	252
2000	237
2500	210
3000	188
4000	157

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: Actual Impedance specification is 51.5 +/- 2 ohms.

Misc. Information (Overall)

Notes (Overall)

Notes: Low Loss, High Flex

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9913F7 B59100	30 MT	5.670 KG	BLACK, MATTE	C	#10 FHDPE SH PVC
9913F7 B591000	305 MT	47.174 KG	BLACK, MATTE	C	#10 FHDPE SH PVC
9913F7 B59250	76 MT	12.587 KG	BLACK, MATTE	C	#10 FHDPE SH PVC
9913F7 B59500	152 MT	23.587 KG	BLACK, MATTE	C	#10 FHDPE SH PVC

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 09-30-2009

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.