

For more Information  
please call

1-800-Belden1



## Description:

RG-8/U type, 13 AWG stranded (7x21) .085" bare copper conductor, polyethylene insulation, bare copper braid shield (97% coverage), non-contaminating PVC jacket.

## Physical Characteristics (Overall)

### Conductor

#### AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	13	7x21	BC - Bare Copper	2.159

### Insulation

#### Insulation Material:

Insulation Material	Wall Thickness (mm)
PE - Polyethylene	7.239

### Outer Shield

#### Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	97

### Outer Jacket

#### Outer Jacket Material:

Outer Jacket Material
PVCNC - Polyvinyl Chloride Non-Contaminating

### Overall Cabling

Overall Nominal Diameter: 10.287 mm

## Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +80°C
UL Temperature Rating:	60°C (UL AWM Style 1354)
Bulk Cable Weight:	147.332 Kg/Km
Max. Recommended Pulling Tension:	845.158 N
Min. Bend Radius (Install)/Minor Axis:	101.600 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMX
CEC/C(UL) Specification:	CMX
AWM Specification:	UL Style 1354 (30 V 60°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes

EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Military Specification:	MIL-C-17D
RG Type:	8/U

### Flame Test

UL Flame Test:	VW-1
----------------	------

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

#### Impedance (Ohm)

52

### Nom. Inductance:

#### Inductance (µH/m)

0.259199

### Nom. Capacitance Conductor to Shield:

#### Capacitance (pF/m)

93.5085

### Nominal Velocity of Propagation:

#### VP (%)

66

### Nominal Delay:

#### Delay (ns/m)

5.05274

### Nom. Conductor DC Resistance:

#### DCR @ 20°C (Ohm/km)

6.2339

### Nominal Outer Shield DC Resistance:

#### DCR @ 20°C (Ohm/km)

3.9372

### Nom. Attenuation:

#### Freq. (MHz) Attenuation (dB/100m)

1	0.6562
10	1.9686
50	4.2653
100	6.2339
200	9.1868
400	13.7802
700	19.3579
900	22.6389
1000	24.2794
4000	76.1192

### Max. Operating Voltage - UL:

#### Voltage

150 V RMS

30 V RMS (UL AWM Style 1354)

### Max. Operating Voltage - Non-UL:

#### Voltage

3700 V RMS

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9251 0101000	305 MT	52.163 KG	BLACK	C	#13 PE BRD PVC
9251 010500	152 MT	26.308 KG	BLACK	C	#13 PE BRD PVC

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 05-14-2007

© 2011 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.