



For more Information
please call

1-800-Belden1



Description:

Tinned copper conductor, PVC insulation. Rated 105°C, 300V. Rated 600V peak for electronic circuits, and internal wiring of electronic and electrical equipment.

Physical Characteristics (Overall)

Conductor

AWG:

| # Conductors | AWG | Stranding | Conductor Material |
|--------------|-----|-----------|--------------------|
| 1 | 28 | 7x36 | TC - Tinned Copper |

Insulation

Insulation Material:

| Insulation Material | Wall Thickness (mm) | Min. Avg. Wall (mm) |
|--------------------------|---------------------|---------------------|
| PVC - Polyvinyl Chloride | 0.406 | 0.381 |

Overall Insulation

Overall Cabling

Overall Nominal Diameter: 1.194 mm

Mechanical Characteristics (Overall)

Bulk Cable Weight: 2.232 Kg/Km

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AWM Specification: UL Style 1007 (300 V 80°C), UL Style 1569 (300 V 105°C)

UL Rating: 300 V RMS, 80°C and 300 V, 105°C

CSA Rating: 300 V RMS, 105°C

CSA Type: TRSR-64

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 10/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: VW-1

CSA Flame Test: FT1

Plenum/Non-Plenum

Plenum (Y/N): No

Related Documents:

No related documents are available for this product

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|--------------|--------|-------------|-------------|-------|-----------------|
| 9928 001100 | 30 MT | 0.091 KG | BROWN | | 28 STR PVC BRN |
| 9928 0011000 | 305 MT | 0.907 KG | BROWN | P | 28 STR PVC BRN |
| 9928 002100 | 30 MT | 0.091 KG | RED | | 28 STR PVC RED |
| 9928 0021000 | 305 MT | 0.907 KG | RED | P | 28 STR PVC RED |
| 9928 003100 | 30 MT | 0.091 KG | ORANGE | | 28 STR PVC ORG |
| 9928 0031000 | 305 MT | 0.907 KG | ORANGE | P | 28 STR PVC ORG |
| 9928 004100 | 30 MT | 0.091 KG | YELLOW | | 28 STR PVC YEL |
| 9928 0041000 | 305 MT | 0.907 KG | YELLOW | P | 28 STR PVC YEL |
| 9928 005100 | 30 MT | 0.091 KG | GREEN, DARK | | 28 STR PVC GRN |
| 9928 0051000 | 305 MT | 0.907 KG | GREEN, DARK | P | 28 STR PVC GRN |
| 9928 007100 | 30 MT | 0.091 KG | VIOLET | | 28 STR PVC VIO |
| 9928 0081000 | 305 MT | 0.907 KG | GRAY | P | #28 STR PVC GRY |
| 9928 009100 | 30 MT | 0.091 KG | WHITE | | 28 STR PVC WHT |
| 9928 0091000 | 305 MT | 0.907 KG | WHITE | P | 28 STR PVC WHT |
| 9928 010100 | 30 MT | 0.091 KG | BLACK | | 28 STR PVC BLK |
| 9928 0101000 | 305 MT | 0.907 KG | BLACK | P | 28 STR PVC BLK |
| 9928 013100 | 30 MT | 0.091 KG | BLUE, DARK | | 28 STR PVC DBLU |
| 9928 0131000 | 305 MT | 0.907 KG | BLUE, DARK | P | 28 STR PVC DBLU |

Notes:

P = STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M' FOR 1 OR 2 STRIPES. 10000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL

Revision Number: 4 Revision Date: 03-01-2010

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.