



Panasonic
ideas for life

**FLAT/VERTICAL TYPE
HIGH POWER
BIFURCATED CONTACT**


NC RELAYS




4 Form C Flat type



2 Form C Flat type



4 Form C Slim type
(PC board)



2 Form C Slim type
(PC board)

FEATURES

1. Compact, slim design

Use of high-performance flat electromagnetic design achieves 10.9 mm .429 inch profile, flat type thin package. Slim type, with width of 11.2 mm .441 inch, enables high-density mounting on PC boards.

2. High reliability

Provides stable contact pressure needed for card lift-off contact driver method. The use of Ac clad twin contacts provides stable contact resistance and ensures high contact reliability.

3. 2-coil latching types available

4. Compatible with all major safety standards

UL and CSA certified, and complies with Japanese Electrical Appliance and Material Control Law.

TYPICAL APPLICATIONS

1. Information processing and telecom equipment such as computers and terminal devices.

2. Gas hot air heating equipment and air conditioners.

3. Timer, temperature controller and other equipment that requires form factor reduction.

4. Transmission and measuring devices such as facsimile machines and electronic counting devices.

5. Control panels for industrial equipment such as machine tools, factory automation devices, and NC machines.

ORDERING INFORMATION

NC D - -

2: 2 Form C
4: 4 Form C

Nil: Standard type
EB: Amber sealed type

D: Twin (bifurcated) contact

Nil: Slim type
J: Flat type

Nil: Plug-in type
P: PC board type

Nil: Single side stable
L2: 2 coil latching


Coil voltage
DC 3, 5, 6, 12, 24, 48, 100V
AC 12, 24, 48, 100V

Notes: 1. UL/CSA approved type is standard.
2. Amber sealed types are sealed and filled with inert gas (nitrogen gas).
Sealed construction with terminals, case and base sealed shut with sealing resin.

TYPES

<Standard type>

1. Flat type (PC board terminal)

Contact arrangement	Nominal coil voltage	Single side stable	 2 coil latching
		Part No.	Part No.
2 Form C	12V AC	NC2D-JP-AC12V	—
	24V AC	NC2D-JP-AC24V	—
	48V AC	NC2D-JP-AC48V	—
	100V AC	NC2D-JP-AC100V	—
	3V DC	NC2D-JP-DC3V	NC2D-JPL2-DC3V
	5V DC	NC2D-JP-DC5V	NC2D-JPL2-DC5V
	6V DC	NC2D-JP-DC6V	NC2D-JPL2-DC6V
	12V DC	NC2D-JP-DC12V	NC2D-JPL2-DC12V
	24V DC	NC2D-JP-DC24V	NC2D-JPL2-DC24V
	48V DC	NC2D-JP-DC48V	NC2D-JPL2-DC48V
100V DC	NC2D-JP-DC100V	NC2D-JPL2-DC100V	
4 Form C	12V AC	NC4D-JP-AC12V	—
	24V AC	NC4D-JP-AC24V	—
	48V AC	NC4D-JP-AC48V	—
	100V AC	NC4D-JP-AC100V	—
	3V DC	NC4D-JP-DC3V	NC4D-JPL2-DC3V
	5V DC	NC4D-JP-DC5V	NC4D-JPL2-DC5V
	6V DC	NC4D-JP-DC6V	NC4D-JPL2-DC6V
	12V DC	NC4D-JP-DC12V	NC4D-JPL2-DC12V
	24V DC	NC4D-JP-DC24V	NC4D-JPL2-DC24V
	48V DC	NC4D-JP-DC48V	NC4D-JPL2-DC48V
100V DC	NC4D-JP-DC100V	NC4D-JPL2-DC100V	


Standard packing: Carton: 20 pcs.; Case: 200 pcs.

2. Slim type**1) Plug-in type**

Contact arrangement	Nominal coil voltage	Single side stable	 2 coil latching
		Part No.	Part No.
2 Form C	12V AC	NC2D-AC12V	—
	24V AC	NC2D-AC24V	—
	48V AC	NC2D-AC48V	—
	100V AC	NC2D-AC100V	—
	3V DC	NC2D-DC3V	NC2D-L2-DC3V
	5V DC	NC2D-DC5V	NC2D-L2-DC5V
	6V DC	NC2D-DC6V	NC2D-L2-DC6V
	12V DC	NC2D-DC12V	NC2D-L2-DC12V
	24V DC	NC2D-DC24V	NC2D-L2-DC24V
	48V DC	NC2D-DC48V	NC2D-L2-DC48V
100V DC	NC2D-DC100V	NC2D-L2-DC100V	
4 Form C	12V AC	NC4D-AC12V	—
	24V AC	NC4D-AC24V	—
	48V AC	NC4D-AC48V	—
	100V AC	NC4D-AC100V	—
	3V DC	NC4D-DC3V	NC4D-L2-DC3V
	5V DC	NC4D-DC5V	NC4D-L2-DC5V
	6V DC	NC4D-DC6V	NC4D-L2-DC6V
	12V DC	NC4D-DC12V	NC4D-L2-DC12V
	24V DC	NC4D-DC24V	NC4D-L2-DC24V
	48V DC	NC4D-DC48V	NC4D-L2-DC48V
100V DC	NC4D-DC100V	NC4D-L2-DC100V	

Standard packing: Carton: 20 pcs.; Case: 200 pcs.


2) PC board type

Contact arrangement	Nominal coil voltage	Single side stable	 2 coil latching
		Part No.	Part No.
2 Form C	12V AC	NC2D-P-AC12V	—
	24V AC	NC2D-P-AC24V	—
	48V AC	NC2D-P-AC48V	—
	100V AC	NC2D-P-AC100V	—
	3V DC	NC2D-P-DC3V	NC2D-PL2-DC3V
	5V DC	NC2D-P-DC5V	NC2D-PL2-DC5V
	6V DC	NC2D-P-DC6V	NC2D-PL2-DC6V
	12V DC	NC2D-P-DC12V	NC2D-PL2-DC12V
	24V DC	NC2D-P-DC24V	NC2D-PL2-DC24V
	48V DC	NC2D-P-DC48V	NC2D-PL2-DC48V
100V DC	NC2D-P-DC100V	NC2D-PL2-DC100V	
4 Form C	12V AC	NC4D-P-AC12V	—
	24V AC	NC4D-P-AC24V	—
	48V AC	NC4D-P-AC48V	—
	100V AC	NC4D-P-AC100V	—
	3V DC	NC4D-P-DC3V	NC4D-PL2-DC3V
	5V DC	NC4D-P-DC5V	NC4D-PL2-DC5V
	6V DC	NC4D-P-DC6V	NC4D-PL2-DC6V
	12V DC	NC4D-P-DC12V	NC4D-PL2-DC12V
	24V DC	NC4D-P-DC24V	NC4D-PL2-DC24V
	48V DC	NC4D-P-DC48V	NC4D-PL2-DC48V
100V DC	NC4D-P-DC100V	NC4D-PL2-DC100V	

Standard packing: Carton: 20 pcs.; Case: 200 pcs.

<Amber type>


1. Flat type (PC board terminal)

Contact arrangement	Nominal coil voltage	Single side stable	 2 coil latching
		Part No.	Part No.
2 Form C	3V DC	NC2EBD-JP-DC3V	NC2EBD-JPL2-DC3V
	5V DC	NC2EBD-JP-DC5V	NC2EBD-JPL2-DC5V
	6V DC	NC2EBD-JP-DC6V	NC2EBD-JPL2-DC6V
	12V DC	NC2EBD-JP-DC12V	NC2EBD-JPL2-DC12V
	24V DC	NC2EBD-JP-DC24V	NC2EBD-JPL2-DC24V
	48V DC	NC2EBD-JP-DC48V	NC2EBD-JPL2-DC48V
4 Form C	100V DC	NC2EBD-JP-DC100V	NC2EBD-JPL2-DC100V
	3V DC	NC4EBD-JP-DC3V	NC4EBD-JPL2-DC3V
	5V DC	NC4EBD-JP-DC5V	NC4EBD-JPL2-DC5V
	6V DC	NC4EBD-JP-DC6V	NC4EBD-JPL2-DC6V
	12V DC	NC4EBD-JP-DC12V	NC4EBD-JPL2-DC12V
	24V DC	NC4EBD-JP-DC24V	NC4EBD-JPL2-DC24V
48V DC	NC4EBD-JP-DC48V	NC4EBD-JPL2-DC48V	
100V DC	NC4EBD-JP-DC100V	NC4EBD-JPL2-DC100V	

Standard packing: Carton: 20 pcs.; Case: 200 pcs.


2. Slim type

1) Plug-in type

Contact arrangement	Nominal coil voltage	Single side stable	 2 coil latching
		Part No.	Part No.
2 Form C	3V DC	NC2EBD-DC3V	NC2EBD-L2-DC3V
	5V DC	NC2EBD-DC5V	NC2EBD-L2-DC5V
	6V DC	NC2EBD-DC6V	NC2EBD-L2-DC6V
	12V DC	NC2EBD-DC12V	NC2EBD-L2-DC12V
	24V DC	NC2EBD-DC24V	NC2EBD-L2-DC24V
	48V DC	NC2EBD-DC48V	NC2EBD-L2-DC48V
4 Form C	100V DC	NC2EBD-DC100V	NC2EBD-L2-DC100V
	3V DC	NC4EBD-DC3V	NC4EBD-L2-DC3V
	5V DC	NC4EBD-DC5V	NC4EBD-L2-DC5V
	6V DC	NC4EBD-DC6V	NC4EBD-L2-DC6V
	12V DC	NC4EBD-DC12V	NC4EBD-L2-DC12V
	24V DC	NC4EBD-DC24V	NC4EBD-L2-DC24V
48V DC	NC4EBD-DC48V	NC4EBD-L2-DC48V	
100V DC	NC4EBD-DC100V	NC4EBD-L2-DC100V	

Standard packing: Carton: 20 pcs.; Case: 200 pcs.

2) PC board type

Contact arrangement	Nominal coil voltage	Single side stable	 2 coil latching
		Part No.	Part No.
2 Form C	3V DC	NC2EBD-P-DC3V	NC2EBD-PL2-DC3V
	5V DC	NC2EBD-P-DC5V	NC2EBD-PL2-DC5V
	6V DC	NC2EBD-P-DC6V	NC2EBD-PL2-DC6V
	12V DC	NC2EBD-P-DC12V	NC2EBD-PL2-DC12V
	24V DC	NC2EBD-P-DC24V	NC2EBD-PL2-DC24V
	48V DC	NC2EBD-P-DC48V	NC2EBD-PL2-DC48V
4 Form C	100V DC	NC2EBD-P-DC100V	NC2EBD-PL2-DC100V
	3V DC	NC4EBD-P-DC3V	NC4EBD-PL2-DC3V
	5V DC	NC4EBD-P-DC5V	NC4EBD-PL2-DC5V
	6V DC	NC4EBD-P-DC6V	NC4EBD-PL2-DC6V
	12V DC	NC4EBD-P-DC12V	NC4EBD-PL2-DC12V
	24V DC	NC4EBD-P-DC24V	NC4EBD-PL2-DC24V
4 Form C	48V DC	NC4EBD-P-DC48V	NC4EBD-PL2-DC48V
	100V DC	NC4EBD-P-DC100V	NC4EBD-PL2-DC100V

Standard packing: Carton: 20 pcs.; Case: 200 pcs.

RATING

1. Coil data

1) Single side stable type (AC)

No. of poles	Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [$\pm 10\%$] (at 20°C 68°F)	Coil inductance		Nominal operating power	Max. allowable voltage (at 50°C 122°F)
					N.C. condition	N.O. condition		
2 Form C	12V AC	80%V or less of nominal voltage (Initial)	10%V or more of nominal voltage (Initial)	41.5mA	—	—	0.50VA	110%V of nominal voltage
	24V AC			22.5mA	—	—	0.54VA	
	48V AC			14.0mA	—	—	0.67VA	
	100V AC			10.5mA	—	—	1.05VA	
4 Form C	12V AC	80%V or less of nominal voltage (Initial)	10%V or more of nominal voltage (Initial)	92mA	—	—	1.10VA	110%V of nominal voltage
	24V AC			45mA	—	—	1.08VA	
	48V AC			22.5mA	—	—	1.08VA	
	100V AC			13.0mA	—	—	1.30VA	

2) Single side stable (DC)

No. of poles	Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [$\pm 10\%$] (at 20°C 68°F)	Coil resistance [$\pm 10\%$] (at 20°C 68°F)	Nominal operating power	Coil inductance		Max. allowable voltage (at 50°C 122°F)*
							N.C. condition	N.O. condition	
2 Form C	3V DC	80%V or less of nominal voltage (Initial)	10%V or more of nominal voltage (Initial)	120mA	25 Ω	360mW	24.2mH	30.0mH	135%V of nominal voltage
	5V DC			72mA	69.4 Ω	360mW	69.5mH	86.0mH	
	6V DC			60mA	100 Ω	360mW	99.4mH	123mH	
	12V DC			30mA	400 Ω	360mW	388mH	480mH	
	24V DC			15mA	1,600 Ω	360mW	1,590mH	1,970mH	
	48V DC			7.5mA	6,400 Ω	360mW	6,270mH	7,680mH	
4 Form C	100V DC	80%V or less of nominal voltage (Initial)	10%V or more of nominal voltage (Initial)	7.4mA	13,500 Ω	740mW	9,470mH	11,700mH	110%V of nominal voltage
	3V DC			240mA	12.5 Ω	720mW	12.8mH	15.8mH	110%V of nominal voltage
	5V DC			144mA	34.7 Ω	720mW	34.3mH	42.4mH	
	6V DC			120mA	50 Ω	720mW	50.7mH	62.7mH	
	12V DC			60mA	200 Ω	720mW	203mH	252mH	
	24V DC			30mA	800 Ω	720mW	812mH	1,000mH	
	48V DC			15mA	3,200 Ω	720mW	2,820mH	3,480mH	
100V DC	7.4mA	13,500 Ω	740mW	14,100mH	17,400mH				



* At 20°C 68°F (Amber type)

3) 2 coil latching type 

No. of poles	Nominal coil voltage	Set voltage (at 20°C 68°F)	Reset voltage (at 20°C 68°F)	Nominal operating current [$\pm 10\%$] (at 20°C 68°F)		Coil resistance [$\pm 10\%$] (at 20°C 68°F)		Nominal operating power		Coil inductance				Max. allowable voltage (at 50°C 122°F)
										Set coil		Reset coil		
				Set coil	Reset coil	Set coil	Reset coil	Set coil	Reset coil	N.C. condition	N.O. condition	N.C. condition	N.O. condition	
2 Form C	3V DC	80%V or less of nominal voltage (Initial)	80%V or less of nominal voltage (Initial)	265.5mA	265.5mA	11.3Ω	11.3Ω	800mW	800mW	10.8mH	12.4mH	3.85mH	4.01mH	110%V of nominal voltage
	5V DC			159.7mA	159.7mA	31.3Ω	31.3Ω	800mW	800mW	29.1mH	38.4mH	11.0mH	11.5mH	
	6V DC			133.3mA	133.3mA	45.0Ω	45.0Ω	800mW	800mW	42.9mH	49.3mH	17.4mH	18.1mH	
	12V DC			66.7mA	66.7mA	180Ω	180Ω	800mW	800mW	173mH	198mH	62.1mH	64.8mH	
	24V DC			33.3mA	33.3mA	720Ω	720Ω	800mW	800mW	688mH	790mH	278mH	290mH	
	48V DC			16.7mA	16.7mA	2,880Ω	2,880Ω	800mW	800mW	2,370mH	2,730mH	1,230mH	1,280mH	
	100V DC			8.0mA	8.0mA	12,500Ω	12,500Ω	800mW	800mW	10,800mH	12,400mH	5,740mH	5,980mH	
4 Form C	3V DC	80%V or less of nominal voltage (Initial)	80%V or less of nominal voltage (Initial)	535.7mA	535.7mA	5.6Ω	5.6Ω	1,600mW	1,600mW	5.25mH	6.03mH	1.42mH	1.48mH	110%V of nominal voltage (Within 2 min.)
	5V DC			320.5mA	320.5mA	15.6Ω	15.6Ω	1,600mW	1,600mW	13.5mH	15.5mH	3.76mH	3.92mH	
	6V DC			266.7mA	266.7mA	22.5Ω	22.5Ω	1,600mW	1,600mW	20.5mH	23.5mH	4.67mH	4.87mH	
	12V DC			133.3mA	133.3mA	90Ω	90Ω	1,600mW	1,600mW	87.6mH	101mH	16.3mH	17.0mH	
	24V DC			66.7mA	66.7mA	360Ω	360Ω	1,600mW	1,600mW	328mH	376mH	74.9mH	78.1mH	
	48V DC			33.3mA	33.3mA	1,440Ω	1,440Ω	1,600mW	1,600mW	1,350mH	1,550mH	289mH	302mH	
	100V DC			16.0mA	16.0mA	6,250Ω	6,250Ω	1,600mW	1,600mW	5,990mH	6,880mH	1,340mH	1,400mH	

Notes: 1. Two coil latching relay 4 Form C series are for intermittent operation only. Power should be applied to coil continuously for no more than two minutes.
 2. Coil resistance is the measured value at a coil temperature of 20°C 68°F. Compensate coil resistance by $\pm 0.4\%$ for each degree (°C °F) of coil temperature change.
 3. Maximum allowable voltage" is that value at maximum contact rating and maximum ambient temperature.
 The graph shown in the data describes the inter-relationship; care should be taken to prevent the total of ambient temperature and the coil temperature rise from exceeding 120°C 248°F.

2. Specifications

Characteristics	Item	Specifications						
		DC 		AC		DC 		AC
		Single side stable	2 Coil latching	Single side stable	Single side stable	2 Coil latching	Single side stable	
Contact	Arrangement	2 Form C			4 Form C			
	Initial contact resistance, max.	Max. 50 mΩ (By voltage drop 6 V DC 1A)						
	Contact material	Au-clad AgNi type			Au-clad AgNi type			
Rating	Nominal switching capacity (resistive load)	Standard: 5A 250V AC, 5A 30V DC Amber: 3A 250V AC, 5A 30V DC			Standard: 4A 250V AC, 5A 30V DC Amber: 2A 250V AC, 5A 30V DC			
	Max. switching power (resistive load)	Standard: 1,250VA, 150W Amber: 750VA, 150W			Standard: 1,000VA, 150W Amber: 500VA, 150W			
	Max. switching voltage	250 V AC						
	Max. switching current	Standard: 5A Amber: 3A (AC), 5A (DC)			Standard: 4A Amber: 2A (AC), 5A (DC)			
	Nominal operating power	360mW (740mW: 100V DC)	800mW	0.50VA to 1.05VA	720mW*2	1,600mW	1.08VA to 1.30VA	
	Min. switching capacity (Reference value)*1	100μA 1V DC			100μA 1VDC			
Electrical characteristics	Insulation resistance (Initial)	Min. 100MΩ (at 500V DC) Measurement at same location as "Initial breakdown voltage" section.			Min. 100MΩ (at 500V DC) Measurement at same location as "Initial breakdown voltage" section.			
	Breakdown voltage (Initial)	Between open contacts	1,000 Vrms for 1min. (Detection current: 10mA.)			1,000 Vrms for 1min. (Detection current: 10mA.)		
		Between contact sets	1,000 Vrms for 1min. (Detection current: 10mA.)			1,000 Vrms for 1min. (Detection current: 10mA.)		
		Between contact and coil	2,000 Vrms for 1min. (Detection current: 10mA.)			2,000 Vrms for 1min. (Detection current: 10mA.)		
	Temperature rise	Max. 65°C [Max. 85°C (100V AC)] (By resistive method, nominal voltage)						
	Operate time (at 20°C 68°F)	Max. 20ms	Set time: Max. 20ms	Max. 30ms*3	Max. 20ms	Set time: Max. 20ms	Max. 30ms*3	
	Release time (at 20°C 68°F)	Max. 10ms	Reset time: Max. 20ms	Max. 40ms*3	Max. 10ms	Reset time: Max. 20ms	Max. 40ms*3	
Mechanical characteristics	Shock resistance	Functional	Min. 98 m/s ² (Half-wave pulse of sine wave: 11 ms; detection time: 10μs.)					
		Destructive	Min. 980 m/s ² (Half-wave pulse of sine wave: 6 ms.)					
Vibration resistance	Functional	10 to 55 Hz at double amplitude of 1 mm (Detection time: 10μs.)						
	Destructive	10 to 55 Hz at double amplitude of 2 mm						
Expected life	Mechanical	Min. 5×10 ⁷	Min. 5×10 ⁷	Min. 10 ⁷	Min. 5×10 ⁷	Min. 5×10 ⁷	Min. 10 ⁷	
	Electrical (resistive load)	Standard: Min. 10 ⁵ (5A 250V AC), Min. 5×10 ⁵ (5A 30V DC) Amber: Min. 10 ⁵ (3A 250V AC), Min. 5×10 ⁵ (5A 30V DC)			Standard: Min. 10 ⁵ (4A 250V AC), Min. 5×10 ⁵ (5A 30V DC) Amber: Min. 10 ⁵ (2A 250V AC), Min. 5×10 ⁵ (5A 30V DC)			
Conditions	Conditions for operation, transport and storage*4 (Not freezing and condensing at low temperature)	-40°C to +70°C -40°F to +158°F (Max.48V DC), -40°C to +55°C -40°F to +131°F (100V DC)	-40°C to +55°C -40°F to +131°F	-40°C to +60°C -40°F to +140°F*5	-40°C to +55°C -40°F to +131°F		-40°C to +40°C -40°F to +104°F	
	Max. Operating speed	50 cps			50 cps			
Unit weight		16 g .56 oz			18 g .63 oz			

Notes: *

*1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

*2. 100V DC: 740mW

*3. For the AC type, the operate and release time differs depending on the phase of the input and cutoff times.


*4. Refer to "6. Usage, Storage and Transport Conditions" in [AMBIENT ENVIRONMENT section in Relay Technical Information](#).

*5. 100V DC: -40°C to +40°C -40°F to +104°F


REFERENCE DATA (Standard type)

1.-(1) Life curve


(AC/DC load 2 Form C, 4 Form C)



1.-(2) Life curve (AC/DC load 2 Form C)




1.-(3) Life curve (AC/DC load 4 Form C)




2.-(1) Temperature rise characteristics (single side stable)

Measured portion: Inside the coil




2.-(2) Temperature rise characteristics (2 coil latching)


Measured portion: Inside the coil




3. Operate time (single side stable)




4. Release time (single side stable)



5.-(1) Rate of change of pick-up and drop-out voltage (2 Form C single side stable)




5.-(2) Rate of change of pick-up and drop-out voltage (4 Form C single side stable)



6.-(1) Ambient temperature vs Max. continuous voltage

Tested sample:


NC2D-P-DC24 V (2 Form C slim single side stable)



6.-(2) Ambient temperature vs Max. continuous voltage

Tested sample:

NC2D-P-DC110 V (2 Form C slim single side stable),
NC4D-P-DC24 V (4 Form C slim single side stable)




DIMENSIONS (Unit: mm inch)


<Standard type>

Flat type


2 Form C




External dimensions



Schematic (Top view)
Single side stable




PC board pattern (Bottom view)
Single side stable




Note: Single side stable types do not have terminals 3 and 6.

2 coil latching





2 coil latching




Flat type

4 Form C


External dimensions



Schematic (Top view)
Single side stable




PC board pattern (Bottom view)
Single side stable




Note: Single side stable types do not have terminals 3 and 6.

2 coil latching




2 coil latching



Slim type
Plug-in type
2 Form C




External dimensions




Schematic (Bottom view)

Single side stable




2 coil latching




Note: Single side stable types do not have terminals 3 and 6.

Slim type
Plug-in type
4 Form C




External dimensions




Schematic (Bottom view)

Single side stable



2 coil latching




Note: Single side stable types do not have terminals 3 and 6.

Slim type
PC board type
2 Form C




External dimensions




Schematic (Bottom view)

Single side stable




PC board pattern (Bottom view)


Single side stable



2 coil latching





2 coil latching




Note: Single side stable types do not have terminals 3 and 6.


Slim type
PC board type
4 Form C




Schematic (Bottom view)
Single side stable




2 coil latching



PC board pattern (Bottom view)
Single side stable



2 coil latching




Note: Single side stable types do not have terminals 3 and 6.

<Amber sealed type>


Flat type
2 Form C




External dimensions



Schematic (Top view)



PC board pattern (Bottom view)




Note: Single side stable types do not have terminals 3 and 6.


Flat type
4 Form C




External dimensions



Schematic (Top view)



PC board pattern (Bottom view)




Note: Single side stable types do not have terminals 3 and 6.


Slim type
Plug-in type
2 Form C



External dimensions



Schematic (Bottom view)




Note: Single side stable types do not have terminals 3 and 6.


Slim type
Plug-in type
4 Form C



External dimensions



Schematic (Bottom view)




Note: Single side stable types do not have terminals 3 and 6.


Slim type
PC board type
2 Form C




External dimensions



Schematic (Bottom view)




PC board pattern (Bottom view)




Note: Single side stable types do not have terminals 3 and 6.


Slim type
PC board type
4 Form C



Schematic (Bottom view)



PC board pattern (Bottom view)



Note: Single side stable types do not have terminals 3 and 6.

NOTES

1. Because the NC relay is polarized, the positive “+” and negative “-” connections to the coil should be done as indicated on the wiring diagram. If connected incorrectly, it may malfunction or fail to operate.
2. As a 2 coil latching type, under the stipulations of the Japanese Electrical Appliance and Material Control Law, because the terminals of NC relay coils have an insulation distance of more than 1.5 mm, NC relays can be used in power supply operating circuits of up to 100 V. When used in contact circuits, 200 V is the maximum voltage.
3. To maintain insulation between coils of 2 coil latching series, terminals ⑤ and ⑥ for flat series, and terminals ③ and ④ for vertical series should be connected to provide common return.






Figure 1 shows wiring that complies with Japanese Electrical Appliance and Material Control Law stipulations for power supply circuits. At the copper traces on PC boards, between terminals ③ and ④, as shown in Figure 2, apply epoxy resin (to thickness of more than 3 mm) or similarly adhesive to provide insulation.



4. 2 coil latching series 4 Form C are for intermittent operation only. Power should be applied to coils continuously for no more than two minutes. See page 30 for general cautions to be observed regarding latching relays.
5. While NC relays can be used with any transmission-wave current to their operation, due to slight weakening of the force of magnetic attraction, decreased resistance to vibration and shock should be taken into account.
6. The current that energizes the coil in an NC relay is AC type. Because the AC sine waveform is distorted, when testing, it is essential to use a measuring device that can properly characterize the distorted waveform. The operating power of the coil in the 100 V AC 4 Form C type is relatively higher than other NC types of AC relay and consequently, the total current applied through all the contacts should be kept below 10 A.
7. The AC type NC relay has a special magnetic design. As a result, once the a-side contacts have switched, the b-side contacts may once again go into a temporary ON state depending on the coil inrush phase. To ensure that this phenomenon does not occur, it is necessary to carry out sufficient practical testing with relays installed in actual devices.

8. When designing top and bottom view schematic diagrams, note that:
 - 1) “Top view” wiring diagram is indicated for the flat series because terminals can be seen from above.
 - 2) “Bottom view” schematic diagram is indicated for the vertical series because terminals cannot be seen from above.



9. Cautions for close proximity mounting
When using slim series in close proximity, mount all relays facing the same direction. Different mounting directions may cause change in the relay characteristics because NC relays are polarized.

For Cautions for Use, see [Relay Technical Information](#).