Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



8762 Multi-Conductor - Single-Pair Cable

For more Information please call

1-800-Belden1



Description:

20 AWG stranded (7x28) TC conductors, polyethylene insulation, twisted pair, overall Beldfoil® shield (100% coverage), 20 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	20	7x28	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PE - Polyethylene	0.4064

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Туре	Outer Shield Material	Coverage (%)
Beldfoil®	Таре	Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	7x28	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.7112

Overall Cabling

Overall Nominal Diameter: 5.182 mm

Pair

Pair Color Code Chart:



Pair Lay Length & Direction:

Lay Length (mm)	Twists/ft. (twist/m)			
38.09985	26.248			

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C		
UL Temperature Rating:	60°C (UL AWM Style 2092)		
Bulk Cable Weight:	31.550 Kg/Km		
Max. Recommended Pulling Tension:	204.617 N		
Min. Bend Radius (Install)/Minor Axis:	50.800 mm		

Page 1 of 3 05-10-2011

Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



8762 Multi-Conductor - Single-Pair Cable

Applicable Specifications and Agency Compliance (Overall)					
Applicable Standards & Environmental Programs					
NEC/(UL) Specification:	CM				
CEC/C(UL) Specification:	CM				
AWM Specification:	UL Style 2092 (300 V 60°C)				
EU CE Mark:	Yes				
EU Directive 2000/53/EC (ELV):	Yes				
EU Directive 2002/95/EC (RoHS):	Yes				
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004				
EU Directive 2002/96/EC (WEEE):	Yes				
EU Directive 2003/11/EC (BFR):	Yes				
CA Prop 65 (CJ for Wire & Cable):	Yes				
MII Order #39 (China RoHS):	Yes				
Flame Test					
UL Flame Test:	UL1685 UL Loading				
Plenum/Non-Plenum					
Plenum (Y/N):	No				

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm) 56

Nom. Inductance:

Inductance (µH/m) 0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m) 88.587

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m) 160.769

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km) 31.1695

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current
3.9 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8762 060U1000	305 MT	10.433 KG	CHROME		2 #20 PE FS PVC
8762 060U500	152 MT	5.670 KG	CHROME		2 #20 PE FS PVC
8762 060100	30 MT	1.315 KG	CHROME		2 #20 PE FS PVC

Page 2 of 3 05-10-2011

Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



8762 Multi-Conductor - Single-Pair Cable

8762 0601000	305 MT	10.433 KG	CHROME	С	2 #20 PE FS PVC
8762 06010000	3,048 MT	108.863 KG	CHROME	CY	2 #20 PE FS PVC
8762 0602000	610 MT	20.865 KG	CHROME	С	2 #20 PE FS PVC
8762 060250	76 MT	2.835 KG	CHROME		2 #20 PE FS PVC
8762 060500	152 MT	5.443 KG	CHROME	С	2 #20 PE FS PVC

Notes:

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN, MAY CONTAIN 2 PIECES, MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Revision Number: 1 Revision Date: 09-18-2008

© 2011 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.