ALPHA WIRE CUSTOMER PRODUCT SPECIFICATION

			er: B9 2 Page	53043 s	Issue: 1 Issue Date: 8/23/2010 Effective Date: 10/18/2010
Α.	Cor 1)		nponer Condu Insula (1) C	uctor	4 X 1 COND 24 (7/32) AWG TC 0.25 Wall, Nom. PVC, Semi Rigid Alpha Wire Color Code E
			Cond	Color BLACK	Cond Color Cond Color 3 RED
			2	BROWN	4 ORANGE
	2) 3)	a) b) Shi		: Wrap	4 Components Cabled 31.5 Twists/meter (min) Clear Mylar Tape, 25% Overlap, Min. TC BRAID Shield,85% Coverage, Min.
	4)	Jac	Drain ket Color(Ripcoi Print	s)	24 (7/32) AWG TC 0.81 Wall, Nom.,PVC GREY 1 End 810 Denier Nylon ALPHA WIRE-* P/N B953043 0.23MM2 (24AWG) (UL) TYPE CM 105C OR AWM 2464 VW-1 CE ROHS (SEQ METERS) * = Factory Code
B.			ble Sp	ecifications	
	1)	UL a) b)	Comp Overa	onent 1 II	AWM/STYLE 10002 105°C / 300 V _{RMS} AWM/STYLE 2464 80°C / 300 V _{RMS} CM 105°C VW-1 105°C
		IEC			EN 60332-1 Flame Behavior EN 60332-2 Flame Behavior LVD 73/23/EEC Amendment 93/68/EEC
C.	 Environmental Compliance 1) EU Directive 2002/95/EC(R 2) REACH Regulation (EC 190) 				C(RoHS): All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web si for compliance Date of Manufacture. 1907/2006):
					This product does not contain any of the substances listed on the European Unio REACH Substance of Very High Concern (SVHC) candidate list, dated 30 Marcl 2010, in excess of a concentration of 0.1% weight/weight.
D.				chanical Pro	
	1) 2) 3) 4)	Ber Pull Sur	nd Radi Tensio nlight Ro	on esistance	-30 to 105°C 10X Cable Diameter 20.9 Lbs, Maximum Yes
E. F.	Ele(1) 2) 3) 4) 5) 6) Oth	Voli Cap Gro Indi Cor OA	al Prop tage Ra bacitance ound Ca uctance nductor Shield	ating ce apacitance DCR	(For Engineering purposes only) 300 V _{RMS} 104.96 pf/m @1 kHz, Nominal Conductor to Conductor 190.24 pf/m @1 kHz, Nominal 0.6232 μH/m, Nominal 85.28 Ω/Km @20°C, Nominal 16.728 Ω/Km @20°C, Nominal
•••	1)		kaging		Flange x Traverse x Barrel (inches)
desc prod Alph no e beer	ough A cribed uct av a prov vent w n advis	Alpha hereir ailabil /ides t /ill Alp sed of	Wire Con are subj lity. he inform ha be liat the poss	ect to errors or o nation and specifi ble for any dama ibility of such dar	hakes every reasonable effort to ensure their accuracy at the time of publication, information and specifications missions and to changes without notice, and the listing of such information and specifications does not ensure cations herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied ges (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has nages, whether in an action under contract, negligence or any other theory, arising out of or in connection with pecifications described herein.

ALPHA WIRE CUSTOMER PRODUCT SPECIFICATION

Part Number: B953043 Page 2 of 2 Pages		Issue: Issue Date: Effective Date:	1 8/23/2010 10/18/2010	
a) 3280 FT b) 1640 FT c) 328 FT d) 164 FT	18 x 12 x 8 Continuous length 12 x 12 x 3.5 Continuous length 10 x 4 x 3.5 Continuous length 6.5 x 4 x 2.5 Continuous length [Spool dimensions may vary slightly]			

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.