

Main

| | |
|------------------------------------|---|
| Range of product | Harmony XVC4 |
| Product or component type | Complete pre-wired monolithic tower light |
| Beacon or indicator bank unit type | 1 illuminated unit |
| Sound signalling | Without |
| Mounting diameter | 40 mm |
| Component name | XVC |
| Light source | Red LED steady |
| Supply circuit type | AC/DC |

Complementary

| | |
|--|---|
| Material | Polycarbonate (illuminated unit) ABS (acrylonitrile butadiene-styrene) (base unit) PBT + ABS (UL94HB) (top cover) |
| Product mounting | On base |
| [Us] rated supply voltage | 24 V |
| Cable cross section | 0.33 mm ² |
| AWG gauge | 22 |
| Cable length | 500 mm |
| Marking | CE |
| [Uimp] rated impulse withstand voltage | 0.8 kV |
| Current consumption | 25 mA |
| Flashing frequency | 1 Hz |
| Product weight | 0.1 kg |
| Height | 100.5 mm |


Environment

| | |
|--|--|
| Standards | EN/IEC 61000-6-2 EN/IEC 61000-6-3 |
| Product certifications | UL |
| Protective treatment | TC |
| Ambient air temperature for storage | -35...70 °C |
| Ambient air temperature for operation | -10...50 °C |
| Class of protection against electric shock | Class II conforming to EN/IEC 61140 |
| IP degree of protection | IP54 in flat surface installation conforming to EN/IEC 60529 |
| RoHS EUR status | Compliant |
| RoHS EUR conformity date | 0808 |

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



| No. of illuminated units | b Without buzzer (mm) | b Without buzzer (in) |
|--------------------------|-----------------------|-----------------------|
| 1 stage | 100.50 | 3.96 |
| 2 stages | 135.50 | 5.33 |
| 3 stages | 170.50 | 6.71 |
| 4 stages | 205.50 | 8.09 |
| 5 stages | 240.50 | 9.47 |

Pre-assembled and Pre-wired Tower Light

Direct Mounting on Horizontal Support

Panel cut-out

mm
in.

