

Product Description

Standardized interfaces; Cost saving because of quick installation; Easy to connect



Application range

- Automation technology
- Mechanical engineering
- Plant engineering
- Tool shop
- Control engineering

Benefits

- Standardized interfaces
- Cost saving because of quick installation
- Easy to connect

Design

- Sub-D plug, 9-pole
- Metalized housing
- Cable outlet 180° (AX)
- No losable parts
- For cable diameter: 5.0 ... 8.0 mm

Approvals (Norm references)

- Sub-D connection / pin assignment in accordance with PROFIBUS



Product features

- Screwing connection
- Switchable terminating resistor integrated
- Switch can also be operated when the connector is plugged and setting is clearly visible
- When being used as a through connector (two cable connections, node) the switch must be in the "OFF" position, if being as a terminal resistor (one cable connection) the switch must be in the "ON" position
- If the switch is in the "ON" position the outgoing bus cable is disconnected

Technical Data

Dimensions

68 mm x 39.5 mm x 17 mm (LxWxH)

Termination resistor

Resistor combination integrated, connectable with slide switch

Connection type

Screwing

Weight

approx. 40 g

Outgoing cable

180°

Interfaces

PROFIBUS-station: SUB-D socket, 9-pole

PROFIBUS-cable: 4 terminals for wires up to 1,0 mm²

Degree of protection

IP20

Current consumption

max. 12.5 mA

Transmission rate

max. 12 MBit/s

Pollution degree

2

Voltage consumption

4.75 .. 5.25 V DC (device is energized)

Permissible ambient conditions

Surrounding air temperature: 0°C...+60°C Transport and storage temperature: -25°C...+80°C

Relative humidity: max. 75% at +25°C

Article List

Part number	Article designation	Outgoing cable	PG	Pieces / PU
EPIC® Data PROFIBUS Connectors				
21700505	ED-PB-AX	180°	no	1

Footnote:

All product related values as shown are nominal values unless specified differently. Further values, e.g. tolerances we submit on request - if available and released for publication.

Photographs are not to scale and do not represent detailed images of the respective products.

For detailed information please see www.lappautomation.com