

Dormer E550 HSSBSPT Taps Straight Flute

DORMER

ISO 2284

Tap tolerance

In accordance with BS21

Chamfer thread number

3

Cutting rake

7°



Flute geometry

Straight flutes

Surface treatment

Bright

Range

1/8 - 1in

Application

For hand or machine tapping of through or blind holes.

491211

							Price Each
Size x pitch	Cutter diameter (mm)	Overall length (mm)	Flute length (mm)	Shank diameter (mm)	Square A/F (mm)	Order Code	
1/8 x 28	9.728	59	15	8.0	6.3	147-4178	
1/4 x 19	13.157	67	19	10.0	8.8	147-4179	
3/8 x 19	16.662	75	21	12.5	10.0	147-4180	
1/2 x 14	20.955	87	26	16.0	12.5	147-4181	
3/4 x 14	26.441	96	28	20.0	16.0	147-4183	
1 x 11	33.240	109	33	25.0	20.0	147-4184	