



Electronics

a vital part of your world

Find Answers:

Friday, 14 October, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

AMPMODU
 ↳ Post Shunts

AMP 881545-2 Active

Directive 2002/95/EC Compliant

RoHS Compliant

(Corporate P/N: 881545-2)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ▸ General Info ▸ Sales Info ▸ Assembly Subcontractors 	<ul style="list-style-type: none"> ▸ Pricing ▸ Product Availability 	<ul style="list-style-type: none"> ▸ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not reviewed for lead free solder process
Shunt Type:	Novo
Number of Positions:	2
Centerline (mm [in]):	2.54 [0.100]
Contact Mating Area Plating:	Gold (30) over Nickel (30)
Shunt Style:	Open Top
Handle:	With

Other Properties:	
Height (mm [in]):	10.90 [0.429]
Profile:	Low
Housing Color:	Black
Housing Material:	Glass-Filled Nylon
Housing Flammability Rating:	UL 94V-0
Contact Material:	Phosphor Bronze
Termination Resistance (m):	15
Packaging Method:	Loose Piece
Contact Current Rating (Amps.):	3
Temperature Range (°C):	-65 – +105

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

