

Item no.: 870-907  
 Product description: 2-Conductor earth terminal block attention! cannot be commoned!



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	16 (RAIL MOUNTED TERMINAL BLOCK WITH CCC)
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 14 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP@COMPACT CONNECTION
Cross section [mm <sup>2</sup> ]	0.08 - 4 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Wiring method	f
Connection method	CAGE CLAMP@COMPACT CONNECTION
Weight	5.7 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	27.5 mm
Height	1.08 in
Width	5 mm
Width	0.197 in

Depth	44.5 mm
Depth	1.75 in
Strip length from	6 mm
Strip length to	7 mm



Strip length

0.26 in

Attention!

Ground (earth) conductor terminal block cannot be commoned.

Mounting

TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
870-907	ABS	05-HG476175/3-PDA			2,5
870-907	CCA	NL6826			2,5
870-907	cURus	E45172			28-12
870-907	DNV	E-9214			2,5
870-907	GL	17295-00HH			2,5
870-907	KEMA	2143311.01			2,5
870-907	LR	91/20112(E6)			2,5
870-907	PTB	PTB03Atex1188U			4
870-907	RosTest	8189158			4

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected