Precision Thick Film Chip Resistors

ERJ R: 0402, 0603, 0805 ERJ E: 0603, 0805, 1206,

1210, 1812

Type: ERJ 2R, 3R, 6R ERJ 3E, 6E, 8E, 14, 12




Features

- Small size and lightweight
- High reliability
 Metal glaze thick film resistive element and three
 layered electrodes.
- Compatible with placement machines
 Bulk, taping and magazine packaging available
- Suitable for both reflow soldering and flow soldering
- Marking


Four digit marking of resistance value on resistive element side (except 2R, 3R, 6R, 3E Type)

- The power rating for one-K size larger is available for 3E, 6E, 8E type
- Low Resistance Tolerance
 ERJ2R, 3E, 6E, 8E, 14, 12 Series ... ±1%
 ERJ2R, 3R, 6R Series ±0.5%
- Approved under the ISO 9001 system Approved under the QS-9000 system
- Reference Standards
 IEC 60115-8, JIS C 5201-8


■ Explanation of Part Numbers (ERJ2R, 3R, 6R Series, ±0.5 % type)




■ Explanation of Part Numbers (ERJ2R, 3E, 6E, 8E, 14, 12 Series, ±1 % type)



■ Construction



■ Dimensions in mm (not to scale)



Type		Dimensions (mm)						
(inches)	L	W	а	b	t	(1000 pcs.)		
ERJ2R (0402)	1.00±0.05	0.50+0.05	0.20 ^{±0.10}	0.25±0.05	0.35±0.05	0.8 g		
ERJ3R (0603)	1.60 ^{±0.15}	0.80+0.15	0.30 ^{±0.20}	0.30 ^{±0.15}	0.45 ^{±0.10}	2 g		
ERJ6R (0805)	2.00±0.20	1.25 ^{±0.10}	0.40 ^{±0.20}	0.40 ^{±0.20}	0.60±0.10	4 g		
ERJ3EK (0603)	1.60±0.15	0.80+0.15	0.30 ^{±0.20}	0.30±0.15	0.45 ^{±0.10}	2 g		
ERJ6EN (0805)	2.00±0.20	1.25 ^{±0.10}	0.40±0.20	0.40 ^{±0.20}	0.60±0.10	4 g		
ERJ8EN (1206)	3.20+0.05	1.60+0.05	0.50±0.20	0.50±0.20	0.60±0.10	10 g		
ERJ14N (1210)	3.20±0.20	2.50±0.20	0.50±0.20	0.50±0.20	0.60±0.10	16 g		
ERJ12N (1812)	4.50±0.20	3.20±0.20	0.50±0.20	0.50±0.20	0.60±0.10	27 g		
ERJ12S (2010)	5.00 ^{±0.20}	2.50±0.20	0.60 ^{±0.20}	0.60±0.20	0.60 ^{±0.10}	27 g		


Ratings

Type (inches)	Power Rating at 70 °C (W)	Limiting Element Voltage (Maximum RCWV) ⁽¹⁾ (V)	Maximum Overload Voltage ⁽²⁾ (V)	Resistance Tolerance (%)		Ranges (Ω) max.	T.C.R. ×10 ⁻⁶ /°C (ppm/°C)	Standard Resistance Values
		HCWV) ^(v) (V)	remage (1)		10	91	±100	Trodictarios varios
ERJ2R	0.063	50	100	±0.5	100	100 K	±50	E24
(0402)	0,000		, , ,	_0.0	110 K	1 M	±100	
					10	91	±100	
ERJ3R	0.063	50	100	±0.5	100	100 K	±50	E24
(0603)					110 K	1 M	±100	
ERJ6R					10	91	±100	
(0805)	0.1	150	200	±0.5	100	100 K	±50	E24
(0005)					110 K	1 M	±100	
ERJ2RK	0.063	50	100	±1	10	1 M	±100	E24
(0402)	0.000	30	100	±1	10	1 101	1100	L24
ERJ3EK	0.063	50	100	±1	10	1 M	±100	E24,E96
(0603)	(0.1)*	50	100	<u> </u>	10	1 101	100	224,230
ERJ6EN	0.1	150	200	±1	10	2.2 M	±100	E24,E96
(0805)	(0.125)*	100	200	<u> </u>	10	2.2 101	2100	
ERJ8EN	0.125	200	400	±1	10	2.2 M	±100	E24,E96
(1206)	(0.25)*							
ERJ14N	0.25	200	400	±1	10	1 M	±100	E24,E96
(1210)								,
ERJ12N, 12S (1812), (2010)	0.5	200	400	±1	10	1 M	±100	E24,E96

⁽¹⁾ Rated Continuous Working Voltage (RCWV) should be determined from RCWV=√Power Rating × Resistance Values, or Limiting Element Voltage (max. RCWV) listed above, whichever is less.

Power Derating Curve

For resistors operating in ambient temperature above 70 $^{\circ}$ C, power rating should be derated in accordance with the figure to the right.



⁽²⁾ Overload (Short-time Overload) Test Voltage (SOTV) should be determined from SOTV=2.5 × Power Rating or max. Overload Voltage listed above whichever is less.


^{*} Please contact us when resistors guaranteed for high power are needed.

■ Packaging Specifications

Standard Quantity


	, , , ,			
Type (inches)	Thickness (mm)	Punched (Paper) Taping (4 mm pitch)	Embossed Taping (4 mm pitch)	Bulk Case
ERJ2R (0402)	0.35	10000 pcs./reel(2 mm pitch)		
ERJ3R (0603)	0.45	5000 pcs./reel		
ERJ6R (0805)	0.6	5000 pcs./reel		
ERJ2RK (0402)	0.35	10000 pcs./reel(2 mm pitch)		
ERJ3EK (0603)	0.45	5000 pcs./reel		25000 pcs./case
ERJ6EN (0805)	0.6	5000 pcs./reel		10000 pcs./case
ERJ8EN (1206)	0.6	5000 pcs./reel		
ERJ14N (1210)	0.6		5000 pcs./reel	
ERJ12N,12S (1812), (2010)	0.6		5000 pcs./reel	

Taping Reel




	Type	φΑ	φB	φC	W	T
Dimensions (mm)	2R,3R,6R 3EK,6EN, 8EN,14N	180.0-3.0	60 min.	13.0 ^{±1.0}	9.0 ^{±1.0}	11.4 ^{±2.0}
	12N, 12S				13.0±1.0	15.4 ^{±2.0}

Bulk Case



(mm)

Embossed Taping




	Туре	Α		В	,	W	F		Е		P ₁
Dimensions	14N	2.80±0.20	3.	.50±0.20)±0.20 8.00±0.30		3.50±0.05		1 75+0.10		
(mm)	12N	3.50 ^{±0.20}	4.	.80 ^{±0.20}	12.00±0.30		5.50±0.05				4.00 ^{±0.10}
	12S	2.80±0.20	5.	.30±0.20							
										_	
	Туре	P ₂		Po		φ) ₀		t ₂		ϕD_1
Dimensions	Type 14N	P ₂		Po		φ[) ₀		t ₂		φD ₁ 1 min.
Dimensions (mm)		P ₂	5	P ₀	0.10	φ[1.0	t ₂	1	

	Туре	А	В	W	F	E	P ₁	P ₂	P ₀	ϕD_0	Т
	2R	0.70 ^{±0.05}	1.20 ^{±0.05}		3.50 ^{±0.05}		2.00 ^{±0.10}	-	4.00.010	4.50.040	0.52 ^{±0.05}
Dimensions (mm)	3R,3EK	1.10 ^{±0.10}	1.90 ^{±0.10}	0.00.000		4 75.010	4.00:010				0.70 ^{±0.05}
	6R,6EN	1.65 ^{±0.15}	2.50 ^{±0.20}	8.00 ^{±0.20}		3.50=0.03	1.75 ^{±0.10}	$\begin{array}{c ccccc} & & & & & & & & & & & & & & & & &$	$2.00^{\pm0.05}$ $4.00^{\pm0.10}$ $1.$	1.50+0.10	0.84±0.05
	8EN	2.00 ^{±0.15}	3.60±0.20								0.04=

Punched (Paper) Taping

■ Recommended Land Pattern

In case of flow soldering, the land width must be smaller than the Chip Resistor width to control the solder amount properly. Generally, the land width should be 0.7 to 0.8 times (W) of the width of chip resistor. In case of reflow soldering, solder amount can be adjusted, therefore the land width should be set to 1.0 to 1.3 times chip resistor width (W).




Type	Dimensions (mm)					
(inches)	а	b	С			
ERJ2R (0402)	0.5 to 0.6	1.4 to 1.6	0.4 to 0.6			
ERJ3R, 3EK (0603)	0.7 to 0.9	2 to 2.2	0.8 to 1			
ERJ6R, 6EN (0805)	1 to 1.4	3.2 to 3.8	0.9 to 1.4			
ERJ8EN (1206)	2 to 2.4	4.4 to 5	1.2 to 1.8			
ERJ14N (1210)	2 to 2.4	4.4 to 5	1.8 to 2.8			
ERJ12N (1812)	3.3 to 3.7	5.7 to 6.5	2.3 to 3.5			
ERJ12S (2010)	3.6 to 4	6.2 to 7	1.8 to 2.8			

■ Recommended Soldering Conditions

Recommendations and precautions are described below.

- Recommended soldering conditions for reflow
- ·Reflow soldering shall be two times maximum.
- Please contact us for additional information when used in conditions other than those specified.
- ·Please measure temperature of terminations and study solderability for every kind of solder and board, before actual use.



For soldering (Example: Sn/Pb)

	Temperature	Time
Preheating	140 °C to 160 °C	60 s to 120 s
Main heating	Above 200 °C	30 s to 40 s
Peak	235 ± 5 °C	max. 10 s

For lead-free soldering (Example : Sn/Ag/Cu)

1 01 1000 1100 0010	or road froe condening (Example : chip tg/ca)					
	Temperature	Time				
Preheating	150 °C to 180 °C	60 s to 120 s				
Main heating	Above 230 °C	30 s to 40 s				
Peak	max. 260 °C	max. 10 s				

Recommended soldering conditions for flow

	For	soldering	For lead-free soldering		
	Temperature Time		Temperature	Time	
Preheating	140 °C to 160 °C	60 s to 120 s	150 °C to 180 °C	60 s to 120 s	
Soldering	245±5 °C	20 s to 30 s	max. 260 °C	max. 10 s	

- 1. If transient load (heavy load in a short time) like pulse is to be applied, carry out an evaluation and confirmation test with the resistors actually mounted on the board.
 - When a load of more than the rated power is applied under load condition at steady state, it could impair performance and/or reliability of the resistor.
 - Never exceed the specified rated power.
- 2. Chlorine type or other highly-reactive flux is not recommended. Residue could affect performance or reliability of the resistors.
- 3. When using a soldering iron, never let the tip of the soldering iron touch the body of the chip resistor. When using a soldering iron with a tip at a high temperature, solder for as short time as possible (no more than three seconds and up to 350 °C).
- 4. Avoid physical shock to the resistor and nipping of the resistor with hard tool (pliers or tweezers) as it may damage protective coating or the body of the resistor and may affect its performance.