

# MSS7/MVS7

### **DIP 14 Series Reed Relays**

### www.cotorelay.com

### **DESCRIPTION**

Coto Technology's epoxy molded DIP 14 Series offers a variety of contacts and schematics to meet the needs of a wide range of applications. It features the MVS7 models designed for high reliability. The MSS7 DIPs are 1 form A relays equipped with the MYAD all-position mounting switch. With switching up to 50 Watts and a 4000V isolation option, the DIP 14 Series is a relay package that allows for automatic insertion directly on PCBs as well as insertion into standard 14 pin DIP sockets.

#### **FEATURES**

- •All position mercury contacts on some models
- Stable contact resistance over life
- •4000 Vac input-output isolation
- •Bounce free operation
- •High insulation resistance
- Switching speed of 300Hz
- •Long life > 1 billion operations
- •Epoxy molded for automatic board processing

#### **APPLICATIONS**

- ATE
- Process control
- Industrial
- Telecom
- Datacom
- High-end security systems
- Signaling
- Metering

### **SPECIFICATIONS**

MSS7

Molded 4-pin All position Wetted Contacts MVS7

High Dielectric Strength DIP Wetted Contacts

All parameters are at 25°C unless otherwise stated.

Parameters	Conditions	Min	Тур	Max	Min	Тур	Max	Units
Contact Ratings								
Switching Voltage	Max DC/PeakAC Resistive			500			10001	Volts
Switching Current	Max DC/PeakAC Resistive			2			2	Amps
Carry Current	Max DC/PeakAC Resistive			3			3	Amps
Contact Rating	Max DC/PeakAC Resistive		000	50	1000		50	Watts
Life Expectancy	Singnal Level 1V, 10mA 50V. 1A		200		1000	0		x106 x106
	500V, 1A					2 5		x106 x106
Static Contact Resistance	50mV, 10mA		40	100		5	100	mOhms
Contact Material	John V, Tollin		Hg	100	-	Hg	100	l lilolillis
Hg Content	·		16			40		mgrams
Relay Specifications		400	1010		4010	10 <sup>12</sup>		
Insulation Resistance	Between all isolated pins at 100V, 25°C, 40% RH	108	1010		10 <sup>10</sup>	1012		Ohms
Capacitance	Across Open Contacts		1.2	2		0.7		pF
Capacitarice	Upper Contact to Coil		1.2			1.5		pF
	Closed Contact to Coil					2.5		pF
	Open Contact to Coil		3	4				pF
Dielectric Strength	Between Contacts	2000						VDC/PeakAC
	Open Contacts				2000			VDC/PeakAC
	Contacts to Coil	5600			5600			VDC/PeakAC
Operate Time	At Nominal Coil Voltage		1.2	1.75		1.5	2.5	ms
(including bounce, DSS7only)	10Hz Square Wave						2.5	
Release Time	Zener-Diode Suppression		1	1.5		1	2.5	ms
Enviromental Ratings								20.2
Storage Temperature		-40		+105	-40		+105	°C
Operating Temperature		-38		+75	-38		+85	°C C
Soldering Temperature	Applied to pins, 5sec. max		+260	40			+260	Gs S
Vibration Resistance <sup>2</sup> (survival)	TO THE REST OF THE PARTY OF THE			10 30			10 30	Gs Gs
Shock Resistance (survival)	11+/- 1ms, 1/2 Sine Wave		2.3	30		2.1	30	grams
Weight		L	2.5		L .	۷.۱		9.41110

<sup>&</sup>lt;sup>1</sup> Current limited up to 5mA, minimum 20 million operations; for frurther information consult factory

<sup>2</sup> Use caution not to exceed vibration resistance limits while ultrsonically cleaning relays with DYAD switches.



# MSS7/MVS7

# DIP 14 Series Reed Relays


## www.cotorelay.com

### **COIL SPECIFICATIONS**

	Contact Form	Coi	oil Voltage Coil			Resistance Operate V		ate Vol	Voltage				Nomina	al Input	Power	
Units		Volts			Ohms		Volts			Volts			mW			
Conditions					+/- 10% (25°C)			Must operate by (25°C)			Must release by (25°C)					
Part #		Min	Тур	Max	Min	Тур	Max	Min	Тур	Max	Min	Тур	Max	Min	Тур	Max
MSS71A05 MSS71A12 MSS71A24	1 Form A 1 Form A 1 Form A		5 12 24	11 21 43	126 450 1935	140 500 2150	154 550 2365	0.5 1 2		3.75 9 18	0.5 1 2		3.75 9 18		179 288 268	
MVS71A05(S) MVS71A12(S) MVS71A24(S	1 Form A 1 Form A 1 Form A		5 12 24	7 15 30	94.5 450 1935	105 500 2150	116 550 2365	0.5 1 2		3.75 9 18	0.5 1 2		3.75 9 18		238 288 268	

### **ORDERING INFORMATION**

A complete part number is represented by the digits below







# DIP 14 Series Reed Relays


## www.cotorelay.com


### **MECHANICAL DIMENSIONS**


Dimensions in inches [mm]











MVS7 must be mounted veritcally. Pin #1 is up.