


---

Item no.: 870-501  
Product description: Double deck terminal block through/through I/I housing color:  
gray

---



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	16 (RAIL MOUNTED TERMINAL BLOCK WITH CCC)
Number of levels	2
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 14 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®COMPACT CONNECTION
Cross section [mm <sup>2</sup> ]	0.08 - 4 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Wiring method	f
Connection method	CAGE CLAMP®COMPACT CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	24 A
Weight	9.584 g
Color	grey
Wiring type	Front-entry
No. of connection Points	4

No. of potentials	2
Height	40 mm
Height	1.57 in
Width	5 mm



Width	0.197 in
Depth	70 mm
Depth	2.76 in
Strip length from	6 mm
Strip length to	7 mm
Strip length	0.26 in
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
870-501	ABS	05-HG476175/3-PDA	500	24	2,5
870-501	BV	07436/Co	500	24	2,5
870-501	CCA	NL6826	500	24	2,5
870-501	cURus	E45172	300	20	28-12
870-501	DNV	E-9214	500	24	2,5
870-501	GL	17295-00HH	500	24	2,5
870-501	KEMA	2143311.01	500	24	2,5
870-501	LR	91/20112(E6)	500	24	2,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected