


## AST024

Spring clamp terminal block, solderable, centerline 3.81 mm / 0.150 inches, horizontal wire entry

### Technical Data

V / A / AWG	150 / 7 / 28 - 20		
0.08 - 0.5 mm <sup>2</sup>	130 V / 2.5 kV / 6 A		
Insulation co-ordination according to EN 60664-1			
Clearance and creepage distances	min. 3 mm		
Insulating material class	CTI 600		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	200	500	500
Rated test voltage	2.5	4	2.5
Protection category according to IEC 529			
	IP20		
Min. insul. strip length	6 mm		
Solder pin dimension	0.8 x 0.8 mm		
Recommended pc board hole dia.	Ø 1.3 mm		
Solder pin length	5 mm		
Pole size	2 - 24		
Color	grey		

Dimensions in mm 1 mm = 0.0394 in.



L = (pole size - 1) x centerline + 3 mm / 0.118 inches

### Part numbers (P/N)

(information: page 16)

Complete the part number by adding the pole size.

#### AST024

centerline 3.81 mm / 0.150 inches

P/N AST024

<input type="checkbox"/>	02	03	04	05	06	07	08
<input type="checkbox"/>	09	10	11	12	13	14	15
<input type="checkbox"/>	17	18	19	20	21	22	23
<input type="checkbox"/>	24						

- Standard pole sizes
- Available on demand. Minimum order quantity 5000 pieces per item.