

MATERIAL SAFETY DATA SHEET ULTRASOLVE AEROSOL

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME ULTRASOLVE AEROSOL
PRODUCT NO. ULS-a
EULS200D
EULS400D
ZE
APPLICATION Cleaning Product
SUPPLIER H K WENTWORTH PTY
LIMITED
P.O. BOX 339
BROOKVALE, NSW 2100
AUSTRALIA
TEL: 02 9938 1566
FAX: 02 9938 1467
GENERAL MANAGER
EMERGENCY TELEPHONE Tel: 029938 1566 between 8.30am and 5.00pm EST
PROPER SHIPPING NAME AEROSOLS (CYCLOHEXANE)

2 HAZARDS IDENTIFICATION

RISK PHRASES

R11 Highly flammable.
R36/38 Irritating to eyes and skin.
R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67 Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

S16 Keep away from sources of ignition - No smoking.
S23 Do not breathe vapour/spray.
S24/25 Avoid contact with skin and eyes.
S37 Wear suitable gloves.
S38 In case of insufficient ventilation, wear suitable respiratory equipment.
A1 Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2 Do not spray on a naked flame or any incandescent material.
S2 Keep out of the reach of children.

The above phrases are the risks associated with the product

PHYSICAL AND CHEMICAL HAZARDS

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

STATEMENT OF HAZARDOUS NATURE

HAZARDOUS SUBSTANCE (According to criteria of NOHSC). DANGEROUS GOODS (According to ADG Code).

DG CLASS

Class 2: Gases

PACKING GROUP N/A

UN NO. 1950

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548)
CYCLOHEXANE	203-806-2	110-82-7	30-60%	F;R11 Xn;R65 Xi;R38 R67 N;R50/53
PROPAN-2-OL	200-661-7	67-63-0	10-30%	F;R11 Xi;R36 R67

ULTRASOLVE AEROSOL

1-METHOXY-2-PROPANOL	203-539-1	107-98-2	10-30%	R10 R67
HEXANE MIXTURE OF ISOMERS (MAX 5% n-HEXANE (203-777-6))	-	-	5-10%	F;R11 Xn;R65 Xi;R38 R67 N;R51/53
HEPTANE	205-563-8	142-82-5	1-5%	F;R11 Xn;R65 Xi;R38 R67 N;R50/53
CARBON DIOXIDE	204-696-9	124-38-9	1-5%	-
HEXANE-norm	203-777-6	110-54-3	< 1%	F;R11 Repr. Cat. 3;R62 Xn;R48/20,R65 Xi;R38 R67 N;R51/53

The Full Text for all R-Phrases is Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels Ingredients are registered on AICS

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

INGESTION

Immediately rinse mouth and provide fresh air.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk.

UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Provide good ventilation.

STORAGE PRECAUTIONS

Store at moderate temperatures in dry, well ventilated area.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
1-METHOXY-2-PROPANOL	ES-TWA	100 ppm	369 mg/m3	150 ppm	553 mg/m3	
CARBON DIOXIDE		5000 ppm	9000 mg/m3	30000 ppm	54000 mg/m3	
CYCLOHEXANE		300 ppm	1030 mg/m3			
HEPTANE		400 ppm	1640 mg/m3	500 ppm	2050 mg/m3	
PROPAN-2-OL	ES-TWA	400 ppm	983 mg/m3	500 ppm	1230 mg/m3	

ULTRASOLVE AEROSOL

INGREDIENT COMMENTS

Australian exposure limits are: LT= ES-TWA and ST= ES STEL

PROTECTIVE EQUIPMENT



ENGINEERING MEASURES

Provide adequate ventilation. Observe Occupational Exposure Limits and minimise the risk of inhalation of vapours.

RESPIRATORY EQUIPMENT

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved chemical safety goggles where eye exposure is reasonably probable.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. **DO NOT SMOKE IN WORK AREA!**

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol Liquid
COLOUR	Colourless
ODOUR	Lemon
VOLATILITY DESCRIPTION	Volatile.
SOLUBILITY	Insoluble in water
BOILING POINT (°C)	>80 (176 F)
MELTING POINT (°C)	-29 (-20.2 F)
RELATIVE DENSITY	0.780 @ 20 °c (68 F)
VAPOUR PRESSURE	11.5 kPa @ 20 °c (68 F)
FLASH POINT (°C)	0 (32 F) CC (Closed cup).
AUTO IGNITION TEMPERATURE (°C)	> 250 (482 F)
FLAMMABILITY LIMIT - LOWER(%)	0.6
FLAMMABILITY LIMIT - UPPER(%)	8.3

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalis.

11 TOXICOLOGICAL INFORMATION

TOXICOLOGICAL INFORMATION

No information available.

INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

SKIN CONTACT

Irritating to skin. Prolonged or repeated exposure may cause severe irritation. Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin.

ULTRASOLVE AEROSOL

EYE CONTACT

Irritating to eyes.

OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

ROUTE OF ENTRY

Inhalation: Skin and/or eye contact.

Name	HEPTANE
Toxic Dose 1 - LD 50	222 mg/kg (ivn-mouse)
Toxic Conc. - LC 50	103 ppm/4h (inh-rat)
Name	CYCLOHEXANE
Toxic Dose 1 - LD 50	12705 mg/kg (oral rat)
Toxic Dose 2 - LD 50	813 mg/kg (oral-mouse)
Name	HEXANE-norm
Toxic Dose 1 - LD 50	28700 mg/kg (oral rat)
Toxic Conc. - LC 50	48000 ppm/4h (inh-rat)
Name	PROPAN-2-OL
Toxic Dose 1 - LD 50	5045 mg/kg (oral rat)
Toxic Dose 2 - LD 50	3600 mg/kg (oral-mouse)
Toxic Conc. - LC 50	47-73 mg/l/4h (inh-rat)
Name	1-METHOXY-2-PROPANOL
Toxic Dose 1 - LD 50	5200 mg/kg (oral rat)
Toxic Dose 2 - LD 50	11700 mg/kg (oral-mouse)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

Name	HEPTANE
LC 50, 96 Hrs, Fish mg/l	4.924
Name	CYCLOHEXANE
LC 50, 96 Hrs, Fish mg/l	42.3
Name	PROPAN-2-OL
LC 50, 96 Hrs, Fish mg/l	9600
EC 50, 48 Hrs, Daphnia, mg/l	10000
Name	1-METHOXY-2-PROPANOL
LC 50, 96 Hrs, Fish mg/l	20800
EC 50, 48 Hrs, Daphnia, mg/l	23300

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements. Empty containers must not be burned because of explosion hazard.

14 TRANSPORT INFORMATION



PROPER SHIPPING NAME	AEROSOLS (CYCLOHEXANE)
ADG CLASS	Class 2.1: Flammable gases
UN NO.	1950
ADG CLASS NO.	2
DG CLASS	Class 2: Gases
PACKING GROUP	N/A

ULTRASOLVE AEROSOL

TUNNEL RESTRICTION CODE	(D)
ADG LABEL NO.	2.1
UN NO. SEA	1950
IMDG CLASS	2.1
IMDG PACK GR.	N/A
EMS	F-D, S-U
UN NO. AIR	1950
AIR CLASS	2.1
AIR PACK GR.	N/A

15 REGULATORY INFORMATION

LABELLING



Irritant



Highly Flammable



Dangerous for the environment

RISK PHRASES

R11	Highly flammable.
R36/38	Irritating to eyes and skin.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S24/25	Avoid contact with skin and eyes.
S37	Wear suitable gloves.
S38	In case of insufficient ventilation, wear suitable respiratory equipment.
A1	Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children.

POISONS SCHEDULE NUMBER NONE

NATIONAL REGULATIONS AND REFERENCES

National Model Regulations for the Control of Workplace Hazardous Substances.
National Code of Practice for the Control of Workplace Hazardous Substances.
National Code of Practice for the Labelling of Workplace Substances.
National Code of Practice for the Preparation of Material Safety Data Sheets.
Approved Criteria for Classifying Hazardous Substances.
Exposure Standards for Atmospheric Contaminants in the Occupational Environment.
Australian Dangerous Goods Code. The Standard for the Uniform Scheduling of Drugs and Poisons (SUSDP).

16 OTHER INFORMATION

ISSUED BY

Helen O'Reilly

REVISION DATE NOVEMBER 2010

REV. NO./REPL. SDS 3

GENERATED

SDS NO. 10617

ULTRASOLVE AEROSOL

RISK PHRASES IN FULL

R10	Flammable.
R48/20	Harmful: danger of serious damage to health by prolonged exposure through inhalation.
R65	Harmful: may cause lung damage if swallowed.
R11	Highly flammable.
R36	Irritating to eyes.
R38	Irritating to skin.
R62	Possible risk of impaired fertility.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.