



3 POLE M12



WIDOK OD STRONY DRUTOW
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
3	Niebieski	BU
4	Czarny	BK


4 POLE M12



WIDOK OD STRONY DRUTOW
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
2	Biały	WH
3	Niebieski	BU
4	Czarny	BK




5 POLE M12



WIDOK OD STRONY DRUTOW
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
2	Biały	WH
3	Niebieski	BU
4	Czarny	BK
5	Szary	GY

PART No MATRIX



WIDOK OD STRONY CZOLA
VIEW FROM FRONT SIDE

TABELA 1
CHART 1

MOLEX PN	WOODHEAD PN	L(mm)	POLE
1200200002	W03007P03M020	2000±25	3 POLE
1200798004	W04007E03M050	5000±25	4 POLE
1200798005	W04007P03M050	5000±25	4 POLE
1200798020	W04007P03M100	10000±50	4 POLE

UWAGI:

- DLUGOSC CIECIA PRZEWODOW I SPECYFIKACJE NABIJANIA WEDLUG LISTY CIECIA.

NOTES:

- FOR WIRES CUTTING LENGTHS AND CRIMPING SPECIFICATION SEE THE CUTTING LIST.

ORIGINAL RELEASE EC NO: DRWN:MSPIEWA CHKD: APPR:	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ∇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE 1	DESIGN UNITS	FIRST ANGLE PROJECTION		
			mm	INCH	DRAWN BY M.DABROWSKA	DATE 2008/10/29	TITLE UL.M12-XP-M-90-XXM-PUR				
			4 PLACES ±	±	CHECKED BY	DATE	APPROVED BY M.WOLSZCZAK				
			3 PLACES ±	±	DATE 208/10/29		MOLEX INCORPORATED				
	2 PLACES ±	±	ANGULAR ± °		MATERIAL NO. SEE CHART 1		DOCUMENT NO. W0X007XXXMXXX		SHEET NO. 1 OF 1		
	1 PLACE ±	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				