


Metal D Type IDC Connectors

Unthreaded



Dimensions : Millimetres (Inches)

Specifications:

Electrical:

Frequency range : DC-1GHz
Nominal impedance : 75 Ω

Materials:

Bodies : Brass per JIS-C3604
Center contact : Brass per JIS-C3604
Insulation : Teflon per ASTM D1457 and ASTM D1710

Environmental:

Operating temperature range : -65°C to +165°C

Specification Table

Description	Material	Finish	Part Number
Nut	Brass	Nickel	13-29-7 75OHM
Washer	Steel		
Insulation	POM	None	
Body	Brass	Nickel 100 m Inches Minimum	
Insulation	ABS	None	
Center Contact	Brass	Gold	
Washer		Nickel	

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.