



10 A **SLIM POWER RELAY**

FL ① LK-P RELA

FEATURES

1. High switching capacity: 10 A 277V AC

2. High insulation resistance between contact and coil

1) Creepage distance and clearances between contact and coil: Min. 6 mm .236 inch (In compliance with IEC65) 2) Surge withstand voltage between contact and coil: 10,000 V or more

3. High noise immunity realized by the card separation structure between contact and coil

4. Popular terminal pitch in AV equipment field

5. Space-saving slim type

Base area: Width 11 × Length 24 mm Width .433 × Length .945 inch

6. Conforms to the various safety standards

UL/CSA, VDE, TÜV and SEMKO, SEV approved

SPECIFICATIONS

Contact			
Arrangement		1 Form A	
Initial contact resis (By voltage drop 6		Max. 100 mΩ	
Contact material		AgSnO ₂ type	
Rating (resistive load)	Nominal switching capacity	10 A 277 V AC, 5 A 30V DC	
	Max. switching power	2,770 V A, 150W	
	Max. switching voltage	277 V AC, 30 V DC	
	Max. switching current	10 A (AC), 5A (DC)	
	Min. switching capacity ^{#1}	100 mA, 5 V DC	
Expected life (min. operations)	Mechanical (at 180 cpm)	2×10^{6}	
	Electrical (at 20 cpm) (at rated load)	105	

Coil

Nominal operating power	530 mW

#1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

Remarks

- Specifications will vary with foreign standards certification ratings.
- *1 Measurement at same location as "Initial breakdown voltage" section.
- *2 Detection current: 10mA
- \star_3 Wave is standard shock voltage of $\pm 1.2 \times 50 \mu s$ according to JEC-212-1981
- *4 Excluding contact bounce time. *5 Half-wave pulse of sine wave: 11 ms; detection time: 10 μs
- *6 Half-wave pulse of sine wave: 6 ms
- *7 Detection time: 10 μs
- *8 Refer to "6. Usage, Storage and Transport Conditions" in AMBIENT ENVIRONMENT section in Relay Technical Information.

TYPICAL APPLICATIONS

- · Audio visual equipment TVs, VTRs
- Office equipment
- LBP, CRT
- Home appliances Refrigerator, Air conditioner

ORDERING INFORMATION EV IKP 12 F

Ex. LKP 1a	F — 1	12V		
Contact arrangement	Protective construction	Coil voltage(DC)		
1a: 1 Form A	F: Flux-resistant type	5, 6, 9, 12, 18, 24V		

UL/CSA, TÜV, SEMKO, TV-5 approved type is standard.

Notes 1. Standard packing Carton: 100 pcs. Case: 500 pcs.

2. 5 V, 9 V, 18 V DC types are also available. Please consult us for details.

1

Characteristics


Max. operati	ng speed		20 cpm (at rated load)						
Initial insulat	ion resista	ance	Min. 1,000 MΩ (at 500 V DC)						
Initial *2 breakdown	Between open contacts			1,000 Vrms for 1 min.					
voltage	Between coil	cor	ntact and	4,000 Vrms for 1 min.					
Initial surge v and coil*3	oltage be	twe	Min. 10,000 V						
Operate time	e*4 (at non	nina	l voltage)	Max. 15 ms (at 20°C 68°F)					
Release time (at nominal v		dioc	Max. 5 ms (at 20°C 68°F)						
Temperature	e rise (at 7	0°C	Max. 45°C with nominal coil voltage and at 10 A contact carrying current (resistance method)						
Fu		Fu	nctional*₅	Min. 200 m/s²{approx. 20 G}					
SHOCK TESISI	Shock resistance		structive*6	Min. 1,000 m/s ² {approx. 100 G}					
Vibration roo	-		nctional*7	10 to 55Hz at double amplitude of 1.5mm					
Vibration resistance		Destructive		10 to 55Hz at double amplitude of 1.5mm					
Conditions for operation, transport and storage*8			Ambient temp.	−40°C to +70°C −40°F to +158°F					
(Not freezing	(Not freezing and		Humidity	5 to 85% R.H.					
condensing at low temperature)			Air pressure	86 to 106 kPa					
Unit weight			Approx. 12 g .42 oz						


TYPES AND COIL DATA (at 20°C 68°F)

Part No.	Nominal voltage, V DC	Pick-up voltage V DC (max.) (Initial)	Drop-out voltage V DC (min.) (Initial)	Coil resistance, Ω (±10%)	Nominal operating current, mA (±10%)	Nominal operating power, mW	Max. allowable voltage, V DC (at 20°C 68°F)
LKP1aF-5V	5	3.5	0.5	47	106.4	530	6.5
LKP1aF-6V	6	4.2	0.6	68	88.3	530	7.8
LKP1aF-9V	9	6.3	0.9	153	58.8	530	11.7
LKP1aF-12V	12	8.4	1.2	272	44.2	530	15.6
LKP1aF-18V	18	12.6	1.8	611	29.5	530	23.4
LKP1aF-24V	24	16.8	2.4	1,087	22.1	530	31.2

DIMENSIONS(mm inch)







' .433 '

 Dimension:
 General tolerance


 Max. 1mm .039 inch:
 ±0.1 ±.004

 1 to 3mm .039 to .118 inch:
 ±0.2 ±.008

 Min. 3mm .118 inch:
 ±0.3 ±.012

Download CAD Data from our Web site.

PC board pattern (Bottom view)




Tolerance: $\pm 0.1 \pm .004$

Schematic (Bottom view)




REFERENCE DATA


1. Max. switching power




2. Coil temperature rise Sample: LKP1aF-12V, 6 pcs. Point measured: coil inside Contact current: 5 A, 10 A



3. Ambient temperature characteristics and coil applied voltage Contact current: 10 A




4. Life curve Operation frequency: 20 times/min. (ON/OFF = 1.5s: 1.5s) Ambient temperature: room temperature




5. Electrical life test

(10 A 277 V AC, resistive load) Sample: LKP1aF-12V, 6 pcs. Operation frequency: 20 times/min. (ON/OFF = 1.5s: 1.5s) Ambient temperature: 20°C 68°F

Circuit:





ecelecce


5 No. of operations, $\times 10^4$ Max

Âin.

10

Change of pick-up and drop-out voltage

Change of contact resistance



SAFETY STANDARDS

UL/C-UL (Recognized) CSA (Certified)		VDE (Certified)		TV rating (UL/CSA)		TÜV (Certified)		SEMKO (Certified)			
File No.	Contact rating	File No.	Contact rating	File No.	Contact rating	File No.	Rating	File No.	Rating	File No.	Contact rating
E43149	10A 277V AC 5A 30V DC		10A 277V AC 5A 30V DC	4001439 0	10A 250V AC (cos±=1.0)	UL E43149 CSA LR26550	10-5		10A 250V AC (cos∳=1.0) 5A 30V DC (0ms)	807779	3/100A 250V AC 5/40A 250V AC 10A 250V DC

For Cautions for Use, see Relay Technical Information.

2

야